Specifications

Eaton QBHW1025

Catalog Number: QBHW1025

Eaton QB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,30 A,22 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q17,QBHW

General specifications

Product Name
Eaton QB thermal magnetic circuit breaker

Catalog Number
QBHW1025

UPC
786679392102

Product Length/Depth
3.6 in

Product Height
4.8 in

Product Width
1.2 in

Product Weight
0.35 lb

Warranty
1 year

Certifications
UL Listed
CSA Certified

Catalog Notes
HACR rated

Powering Business Worldwide

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

25 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

17

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers

Eaton Specification Sheet - QBHW1025

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia