Specifications

Eaton QBHW2015

Catalog Number: QBHW2015

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 15A, 22 kAIC, 120/240V , Bolt-on

General specifications

Product Name
Eaton QB thermal magnetic circuit breaker

Catalog Number
QBHW2015

UPC
786679392508

Product Length/Depth
3.9 in

Product Height
4.8 in

Product Width
2.1 in

Product Weight
0.55 lb

Warranty
1 year

Certifications
UL Listed
CSA Certified

Catalog Notes
HACR rated

Powering Business Worldwide

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Two-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

15 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

7

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - QBHW2015

Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia