ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

QBHW2100 2 Pole 100A QBHW BRKR

Eaton Corp

Catalog Number	QBHW2100
Manufacturer	Eaton Corp
Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-Pole, 100A, 22 Kaic, 120/240V , Bolt-On
Weight per unit	0.8000 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

Features

amperage rating	100 A
dimensions	4.0000 IN X 2.2000 IN X 4.8000 IN
interrupt rating	22
Poles	2
Trip Type	Non-Interchangeable
Voltage Rating	120/240 V

Descriptions

Description	2 POLE 100A QBHW BRKR
extra long description	ETN QBHW2100 2 Pole 100 Amp QBHW Br
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 100A, 22 kAIC, 120/240V , Bolt-on
Product Type	2 Pole 100 Amp QBHW Breaker

Manufacturer Information

Brand	Eaton
GTIN	00786679393109
Manufacturers Part Number	QBHW2100
UPC	786679393109

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.8

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional EnergyOtherDatacenters - IT Space: CI and Hyper ConvergedGeneration - Renewable Energy - Alternative EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	CSA Certified,UL Listed