Specifications

Eaton QBHW3100H

Catalog Number: QBHW3100H

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 100A, 22 kAIC, 240V, Bolt-on

General specifications

Product Name
Eaton QB thermal magnetic circuit breaker

Catalog Number
QBHW3100H

UPC
786679393659

Product Length/Depth
2.9 in

Product Height
3 in

Product Width
2.9 in

Product Weight
1.1 lb

Warranty
1 year

Certifications
UL Listed
CSA Certified

Catalog Notes
HACR rated

Powering Business Worldwide

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Three-pole

Type

Quicklag

Performance Ratings

Amperage Rating

100 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Quantity

32

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers

Eaton Specification Sheet - QBHW3100H

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia