Specifications

Eaton QC3070H

Catalog Number: QC3070H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker,Industrial circuit breaker,70 A,10 kAIC,Three-pole,240 V,Thermal-magnetic,Cable-in/cable-out,QC,Non-interchangeable

General specifications

Product Name Eaton QC thermal magnetic circuit breaker	Catalog Number QC3070H
	UPC 786679240243
Product Length/Depth 3.8 in	Product Height 4.9 in
Product Width 3.2 in	Product Weight 1.2 lb
Warranty 1 year	Certifications CSA Certified UL Listed

Powering Business Worldwide

Physical Attributes

Circuit breaker type

QC

Connection

Cable-in/cable-out

Number of poles

Three-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

70A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

240 V - 240 V

Miscellaneous

Options

Non-interchangeable

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - QC3070H

Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia