PASS & SEYMOUR®

radiant® Screwless Wall Plates

Modern low-profile Screwless Wall Plates fit for today's homes and hospitality settings.

RWP26, RWP262, RWP263, RWP264, RWP265, RWP266

Part of the redesigned radiant® collection of wiring devices and home automation controls, Legrand's broad offering of screwless wall plates are a step above ordinary with modern low profiles that fit more flush to the wall than standard wall plates. These wall plates color-match radiant® devices and are equipped with one-piece plastic subplates and screws to align devices and ensure proper positioning. Ideal for residential, multi-dwelling, commercial office and hospitality applications, radiant® screwless wall plates are available in one- to six-gang configurations, each in six standard colors and two metallic finishes.

Features & Benefits

Redesigned screwless wall plates feature a lower, more modern profile in keeping with today's design trends.

Molded of rugged .065" thick polycarbonate.

One-piece plastic subplate mounts over the device for easy retrofit and lower profile.

RWP26LA

An extra 3/8" width and height than standard-size wall plates for more tolerance in covering ragged sheet rock openings.

Opening accommodates all NEMA 26-opening devices.

Subplate screws align devices to ensure proper positioning of wall plates.

- **Part of the radiant® collection.**
- **New, lower profile.**
- **Available in Ivory, White, Brown, Gray, Black, and Light Almond; and two metallic finishes** – Nickel, Dark Bronze and Graphite.

3rd Party Compliance

c UL us Listed to UL514. CSA Certified.

Wall Plate Dimensions/Materials



radiant® Screwless Wall Plate



radiant® Screwless Wall Plate Plastic Subplate

Materials

Body Construction	Molded of .065" thick polycarbonate
Sub-plate Construction	Polyphenylene Ether and Polystyrene
Mounting Screws	Steel

radiant® Screwless Polycarbonate Wall Plates

- Available in 26-style openings.
- Extra 3/8" width and height than standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Molded of .065" thick polycarbonate.
- One-piece plastic subplate.
- Available in two metallic finishes and six standard colors.

Wall Plate Dimensions

1 gang	3.15" x 4.94"
2 gang	4.96" x 4.94"
3 gang	6.77" x 4.94"
4 gang	8.59" x 4. 94"
5 gang	10.40" x 4.94"
6 gang	12.21" x 4.94"

Subplate Dimensions

1 gang	1.81" x 4.78" x .15"
2 gang	3.62" x 4.78" x .15"
3 gang	5.44" x 4.78" x .15"
4 gang	7.25" x 4.78" x .15"
5 gang	9.06" x 4.78" x .15"
6 gang	10.87" x 4.78" x .15"

Ordering Information

radiant® Metallic Finish Screwless Wall Plates – Polycarbonate Screwless 26 Openings – Plastic Subplate included

Description	Color	26 Openings
One Gang	Nickel	RWP26NI
	Dark Bronze	RWP26DBCC6
	Graphite	RWP26GCC6
Two Gang	Nickel	RWP262NI
	Dark Bronze	RWP262DBCC6
	Graphite	RWP262GCC6
Three Gang 	Nickel	RWP263NI
	Dark Bronze	RWP263DBCC6
	Graphite	RWP263GCC6
Four Gang 	Nickel	RWP264NI
	Dark Bronze Graphite	RWP264DB RWP264GCC6
Five Gang 	Nickel	RWP265NI
	Dark Bronze Graphite	RWP265DB RWP265G
Six Gang 	Nickel	RWP266NI
	Dark Bronze Graphite	RWP266DB RWP266G

One Gang
Nickel

Two Gang
Dark Bronze



Four Gang
Dark Bronze



Six Gang
Dark Bronze

Ordering Information

radiant® Screwless Wall Plates – Polycarbonate Screwless Wall Plates – Plastic Subplate included

Description	Color	26 Openings
One Gang	Ivory	RWP26I
	White	RWP26W
	Brown	RWP26
	Gray	RWP26GRY
	Black	RWP26BK
	Light Almond	RWP26LA
Two Gang	Ivory	RWP262I
	White	RWP262W
	Brown	RWP262
	Gray	RWP262GRY
	Black	RWP262BK
	Light Almond	RWP262LA
Three Gang	Ivory	RWP263I
	White	RWP263W
	Brown	RWP263
	Gray	RWP263GRY
	Black	RWP263BK
	Light Almond	RWP263LA
Four Gang	Ivory	RWP264I
	White	RWP264W
	Brown	RWP264
	Gray	RWP264GRY
	Black	RWP264BK
	Light Almond	RWP264LA
Five Gang	Ivory	RWP265I
	White	RWP265W
	Brown	RWP265
	Gray	RWP265GRY
	Black	RWP265BK
	Light Almond	RWP265LA
Six Gang	Ivory	RWP266I
	White	RWP266W
	Brown	RWP266
	Gray	RWP266GRY
	Black	RWP266BK
	Light Almond	RWP266LA



One Gang



Two Gang



Three Gang



Four Gang



One Gang Plastic Subplate

Two Gang Plastic Subplate

Screwless 26 Openings Plastic Subplate included

Description	Height	Width
One Gang	4.94"	3.15"
Two Gang	4.94"	4.96"
Three Gang	4.94"	6.77"
Four Gang	4.94"	8.59"
Five Gang	4.94"	10.40"
Six Gang	4.94"	12.21"

Screwless Plastic Subplate Dimensions

Description	Height	Width
One Gang	4.78"	1.81"
Two Gang	4.78"	3.62"
Three Gang	4.78"	5.44"
Four Gang	4.78"	7.25"
Five Gang	4.78"	9.06"
Six Gang	4.78"	10.87"

Vertical Markets

- **Office**
- **Residential**
- **Multiple Dwelling**
- **Hospitality/Lodging**

Also available in the radiant® collection

- **GFCI Receptacles**
- **Standard & Tamper-Resistant Receptacles**
- **Paddle Switches**
- **Lighting & Fan Controls**
- **Timers**
- **Sensors**
- **Combination Devices**
- **USB Charging Devices**
- **Night Lights**
- **Home Automation Controls**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

SF20194 September 2019 **©2019 Legrand All Rights Reserved**

PASS & SEYMOUR®

radiant® Screwless Wall Plates

Modern low-profile Screwless Wall Plates fit for today's homes and hospitality settings.

RWP26, RWP262, RWP263, RWP264, RWP265, RWP266

Part of the redesigned radiant® collection of wiring devices and home automation controls, Legrand's broad offering of screwless wall plates are a step above ordinary with modern low profiles that fit more flush to the wall than standard wall plates. These wall plates color-match radiant® devices and are equipped with one-piece plastic subplates and screws to align devices and ensure proper positioning. Ideal for residential, multi-dwelling, commercial office and hospitality applications, radiant® screwless wall plates are available in one- to six-gang configurations, each in six standard colors and two metallic finishes.

Features & Benefits

Redesigned screwless wall plates feature a lower, more modern profile in keeping with today's design trends.

Molded of rugged .065" thick polycarbonate.

One-piece plastic subplate mounts over the device for easy retrofit and lower profile.

RWP26LA

An extra 3/8" width and height than standard-size wall plates for more tolerance in covering ragged sheet rock openings.

Opening accommodates all NEMA 26-opening devices.

Subplate screws align devices to ensure proper positioning of wall plates.

- **Part of the radiant® collection.**
- **New, lower profile.**
- **Available in Ivory, White, Brown, Gray, Black, and Light Almond; and two metallic finishes** – Nickel, Dark Bronze and Graphite.

3rd Party Compliance

c UL us Listed to UL514. CSA Certified.

Wall Plate Dimensions/Materials



radiant® Screwless Wall Plate



radiant® Screwless Wall Plate Plastic Subplate

Materials

Body Construction	Molded of .065" thick polycarbonate
Sub-plate Construction	Polyphenylene Ether and Polystyrene
Mounting Screws	Steel

radiant® Screwless Polycarbonate Wall Plates

- Available in 26-style openings.
- Extra 3/8" width and height than standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Molded of .065" thick polycarbonate.
- One-piece plastic subplate.
- Available in two metallic finishes and six standard colors.

Wall Plate Dimensions

1 gang	3.15" x 4.94"
2 gang	4.96" x 4.94"
3 gang	6.77" x 4.94"
4 gang	8.59" x 4. 94"
5 gang	10.40" x 4.94"
6 gang	12.21" x 4.94"

Subplate Dimensions

1 gang	1.81" x 4.78" x .15"
2 gang	3.62" x 4.78" x .15"
3 gang	5.44" x 4.78" x .15"
4 gang	7.25" x 4.78" x .15"
5 gang	9.06" x 4.78" x .15"
6 gang	10.87" x 4.78" x .15"

Ordering Information

radiant® Metallic Finish Screwless Wall Plates – Polycarbonate Screwless 26 Openings – Plastic Subplate included

Description	Color	26 Openings
One Gang	Nickel	RWP26NI
	Dark Bronze	RWP26DBCC6
	Graphite	RWP26GCC6
Two Gang	Nickel	RWP262NI
	Dark Bronze	RWP262DBCC6
	Graphite	RWP262GCC6
Three Gang 	Nickel	RWP263NI
	Dark Bronze	RWP263DBCC6
	Graphite	RWP263GCC6
Four Gang 	Nickel	RWP264NI
	Dark Bronze Graphite	RWP264DB RWP264GCC6
Five Gang 	Nickel	RWP265NI
	Dark Bronze Graphite	RWP265DB RWP265G
Six Gang 	Nickel	RWP266NI
	Dark Bronze Graphite	RWP266DB RWP266G

One Gang
Nickel

Two Gang
Dark Bronze



Four Gang
Dark Bronze



Six Gang
Dark Bronze

Ordering Information

radiant® Screwless Wall Plates – Polycarbonate Screwless Wall Plates – Plastic Subplate included

Description	Color	26 Openings
One Gang	Ivory	RWP26I
	White	RWP26W
	Brown	RWP26
	Gray	RWP26GRY
	Black	RWP26BK
	Light Almond	RWP26LA
Two Gang	Ivory	RWP262I
	White	RWP262W
	Brown	RWP262
	Gray	RWP262GRY
	Black	RWP262BK
	Light Almond	RWP262LA
Three Gang	Ivory	RWP263I
	White	RWP263W
	Brown	RWP263
	Gray	RWP263GRY
	Black	RWP263BK
	Light Almond	RWP263LA
Four Gang	Ivory	RWP264I
	White	RWP264W
	Brown	RWP264
	Gray	RWP264GRY
	Black	RWP264BK
	Light Almond	RWP264LA
Five Gang	Ivory	RWP265I
	White	RWP265W
	Brown	RWP265
	Gray	RWP265GRY
	Black	RWP265BK
	Light Almond	RWP265LA
Six Gang	Ivory	RWP266I
	White	RWP266W
	Brown	RWP266
	Gray	RWP266GRY
	Black	RWP266BK
	Light Almond	RWP266LA



One Gang



Two Gang



Three Gang



Four Gang



One Gang Plastic Subplate

Two Gang Plastic Subplate

Screwless 26 Openings Plastic Subplate included

Description	Height	Width
One Gang	4.94"	3.15"
Two Gang	4.94"	4.96"
Three Gang	4.94"	6.77"
Four Gang	4.94"	8.59"
Five Gang	4.94"	10.40"
Six Gang	4.94"	12.21"

Screwless Plastic Subplate Dimensions

Description	Height	Width
One Gang	4.78"	1.81"
Two Gang	4.78"	3.62"
Three Gang	4.78"	5.44"
Four Gang	4.78"	7.25"
Five Gang	4.78"	9.06"
Six Gang	4.78"	10.87"

Vertical Markets

- **Office**
- **Residential**
- **Multiple Dwelling**
- **Hospitality/Lodging**

Also available in the radiant® collection

- **GFCI Receptacles**
- **Standard & Tamper-Resistant Receptacles**
- **Paddle Switches**
- **Lighting & Fan Controls**
- **Timers**
- **Sensors**
- **Combination Devices**
- **USB Charging Devices**
- **Night Lights**
- **Home Automation Controls**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

SF20194 September 2019 **©2019 Legrand All Rights Reserved**