Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

S3951 40W A19 130V Vibr SRV

Satco

Catalog Number	S3951
Manufacturer	Satco
Description	A-Line Incandescent Lamp, 300 LM Brightness (Lumens), 40 W, 130 V, Frosted, C-9 Filament, 2500 H Average Life, Medium Base, Non Dimmable, 2.38 In Diameter, 4-1/8 In Length, 0.1 LB
Weight per unit	0.1000 (lbs/each)
Product Category	Line A, P, PS Shape Lamps

Features

Base	Medium
lumens	300
Shape	A19
Voltage Rating	130

Material, Color, and Finish

Color	White

Dimensions and Weight

Diameter	2.38

Descriptions

Description	40W A19 130V VIBR SRV

Manufacturer Information

GTIN	00045923039515
UPC	045923039515

Taxonomies, Classifications, and Categories

Category Description	INCANDESCENT
Type	General Service

Availability

Manufacturer Status	Inactive
Status	Inactive

Packaging

Carton	2
Package	120
Weight Per each	0.1

Uses, Certifications, and Standards

standard	RoHS Compliant