S8429

F32T8/850/HL/ENV
32 watt; T8; Fluorescent; 5000K Natural Light; 85 CRI; Medium Bi Pin base

Features
- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8429

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8429	045923084294	32	T8	Medium Bi Pin	G13	F32T8/850/HL/ENV	1.00"

MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	IS Rated Hours	RS/PRS Rated Hours	Kelvin Temp
47.78"	48"	3100	3050	30000	24000	30000	5000

Color	Pack	CRI	RoHS Compliant	CEE Qualified
Natural Light	30	85	Yes	Yes

National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051

S8429

F32T8/850/HL/ENV
32 watt; T8; Fluorescent; 5000K Natural Light; 85 CRI; Medium Bi Pin base

Features
- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8429

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8429	045923084294	32	T8	Medium Bi Pin	G13	F32T8/850/HL/ENV	1.00"

MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	IS Rated Hours	RS/PRS Rated Hours	Kelvin Temp
47.78"	48"	3100	3050	30000	24000	30000	5000

Color	Pack	CRI	RoHS Compliant	CEE Qualified
Natural Light	30	85	Yes	Yes

National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051