Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

S9454 15W Led PAR38 5000K 80 Cri 60 Deg 1200LM

Satco

Catalog Number	S9454
Manufacturer	Satco
Description	Led PAR38 Lamp, 60 ° Beam Angle, 80, 5000 K, 1000 LM Brightness (Lumens), 15 W, 120 V, Silver, 25000 H Average Life, E26 Medium Base, Dimmable, 4.75 In Diameter, 5.19 In Length, 50 W, 3 Yr Warranty
Weight per unit	0.7900 (lbs/each)
Product Category	Led Parabolic Reflector Par SH

Features

Base	E26
brightness	1000
lumens	500
Voltage Rating	120

Material, Color, and Finish

Color	Colorless
color rendering index (cri)	80

Dimensions and Weight

Size	5.19

Descriptions

Description	15W LED PAR38 5000K 80 CRI 60 DEG 1200LM

Manufacturer Information

GTIN	00045923094545
UPC	045923094545

Taxonomies, Classifications, and Categories

Category Description	LED PAR SHAPE LAMPS
Type	PAR LED

Availability

Manufacturer Status	Inactive

Packaging

Carton	12
Package	6
Weight Per each	0.79

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)