ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

S9636 11.5W Led BR40 40K 120V Dim

Satco

Catalog Number	S9636
Manufacturer	Satco
Description	Led Lamp, BR40 Shape, 103 ° Beam Angle, 80, 4000 K, 360 LM Brightness (Lumens), 11.5 W, 120 V, Frosted White, 25000 H Average Life, E26 Base, Dimmable, 5 In Diameter, +40 °C Operating Temperature, 0.81 LB
Weight per unit	0.8100 (lbs/each)
Product Category	Led Reflector Gu, MR R Shape L

Features

Base	E26
brightness	360
lumens	525
Voltage Rating	120
Warranty	5 Year Limited - 10 hr per day

Material, Color, and Finish

Color	Frosted White
color rendering index (cri)	80
color temperature	4000

Dimensions and Weight

Diameter	5.000000000000000
Size	6.44

Descriptions

Description	11.5W LED BR40 40K 120V DIM
extra long description	SATCO S9636 11.5BR40/LED/4000K/1000

Manufacturer Information

GTIN	00045923096365
UPC	045923096365

Taxonomies, Classifications, and Categories

Category Description	LED REFLECTOR GU, MR R SHAPE LAMPS
Type	BR LED

Packaging

Carton	6
Package	12
Weight Per each	0.81

Uses, Certifications, and Standards

Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)