ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



SDR4 SCOTCHCODE WIRE MARKER TAPE REFILL ROLL SDR-4

MINNESOTA MINING (3M)

Catalog Number	SDR4
Manufacturer	MINNESOTA MINING (3M)
Description	3M™ ScotchCode™ Wire Marker Tape Refill Roll SDR is available in ten NEMA colors, individual numbers and consecutive numbers, letters and symbols.
Weight per unit	0.0700 (lbs/each)
Product Category	Markers & Marking Tapes

Descriptions

Description	SCOTCHCODE WIRE MARKER TAPE REFILL ROLL SDR-4
Features	3M ScotchCode™ Wire Marker Tape Refill Roll SDR tape features a high tack, acrylic adhesive that resists solvents, oil and water and adheres firmly to insulation surfaces. The SDR tape can be used for applications with operating temperatures between -40°F (-40°C) to 250°F (121°C).
Long Description	3M™ ScotchCode™ Wire Marker Tape Refill Roll SDR is available in ten NEMA colors, individual numbers and consecutive numbers, letters and symbols.
Product Type	3M™ Scotchcode™ Wire Marker Tape Refill Roll
Special Features	Pre-printed
Extra Long Description	3M 7000058258 3M™ ScotchCode™ Wire

Manufacturer Information

Brand	3M Electrical Products
GTIN	00054007093732
Manufacturers Part Number	7000058258
	SDR4
UPC	054007

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Tape Roll Refill

Packaging

Carton	1
Package	10
Weight Per Each	0.0700 (lbs/each)

ScotchCode™

STD Tape Dispenser
SDR Wire Marking Tape
Data Sheet

Application:

ScotchCode™ SDR is a polyester film tape with an acrylic pressure sensitive adhesive, the tape is used in the 3M STD ScotchCode tape dispenser. From the dispenser, the user can pull out and tear off the amount of tape needed for thier particular application such as marking wires, terminal blocks, panels, ect.

Tape Technical Data:

(All Values are Typical Values)

Material:	Polyester film with acrylic pressure sensitive adhesive
Application Temperature Range	32°F to 120°F (0°C to 49°C)
Operating Temperature Range	–40°F to 250°F (–40°C to 121°C)
Storage Temperature (Relative Humidity)	80°F (26°C) 25–50%
Tape Roll Width	0.215 inches (5,46 mm)
Tape Roll Length	96 inches (2,43 m)
Number of Characters	6 per inch (6 per 2,54 cm)
Tape Thickness	3 mils (0,08mm)
Adhesion to Steel (ASTM D–1000)	25 oz./inch width (273 Newtons/Meters)
Adhesion to Backing (ASTM D–1000)	10 oz./inch width (109 Newtons/Meters)

Engineering Specification:

Wire marking tape shall be polyester tape, 3 mils (0,08mm) thick, with acrylic pressure sensitive adhesive. The tape will be in a roll 0.215 inches (5,46mm) wide and 96 inches (2,43m) long, wound on a .38 inch (9,65mm) dia. plastic core. There will be six (6) characters per inch of tape. These rolls will be used with 3M ScotchCode STD tape dispensers and shall be manufactured by 3M.

PRODUCT	DESCRIPTION	PRINTING ON ROLL
SDR–0 thru SDR–9	ScotchCode Wire Marking Tape	0 thru 9
SDR–0–9	0–9 consecutive	1 number/roll
SDR–10–19 thru SDR–90–99	10–19 consecutive thru 90–99 consecutive	1 number/roll thru 1 number/roll
SDR–A thru SDR–Z		A thru Z
SDR–L1		L1
SDR–L2		L2
SDR–L3		L3
SDR–T1		T1
SDR–T2		T2
SDR–T3		T3
SDR + (Plus)		+
SDR – (Minus)		–

This tape is also avaibile in ten colors.

	Color of Roll
SDR–BK	BLACK
SDR–BL	BLUE
SDR–BN	BROWN
SDR–GN	GREEN
SDR–GY	GRAY
SDR–OR	ORANGE
SDR–RD	RED
SDR–VL	VIOLET
SDR–WH	WHITE
SDR–YL	YELLOW
SDR–MC	*

* Includes one roll of each of the above colors.

STD–0–9	dispenser filled with numbers 0 thru 9
STD–C	dispenser filled with all ten colors
STD	empty dispenser

STD Tape Dispenser
SDR Wire Marking Tape

Important Notice to Purchaser:

All statements, technical information and recommendations related to the Seller's products are based on information believed to be reliable, but the accuracy or completeness thereof is not guaranteed. Before utilizing the product, the user should determine the suitability of the product for its intended use. The user assumes all risks and liability whatsoever in connection with such use.

Any statements or recommendations of the Seller which are not contained in the Seller's current publications shall have no force or effect unless contained in an agreement signed by an authorized officer of the Seller. The statements contained herein are made in lieu of all warranties expressed or implied, including but not limited to the implied warranties of merchantability and fitness for a particular purpose which warranties are hereby expressly disclaimed.

SELLER SHALL NOT BE LIABLE TO THE USER OR ANY OTHER PERSON UNDER ANY LEGAL THEORY, INCLUDING BUT NOT LIMITED TO NEGLIGENCE OR STRICT LIABILITY, FOR ANY INJURY OR FOR ANY DIRECT OR CONSEQUENTIAL DAMAGES SUSTAINED OR INCURRED BY REASON OF THE USE OF ANY OF THE SELLER'S PRODUCTS.

3M

Electrical Products Division
6801 River Place Blvd.
Austin, TX 78726-9000

Printed on 50% recycled waste paper, including 10% post-consumer waste paper.

Litho in USA.
1-4-94
© 3M 1993 80-6104-