STL110HBW

STEALTH Sensor with twin precision die cast HB101 Bullet floods pre-wired and assembled on universal CU4 cover plate. Accepts PAR38 lamps, 150 watt max. Lamps not supplied.

Color: White

Weight: 5.0 lbs



Technical Specifications

UL Listing:
Suitable for wet locations.

Power Consumption:
1 watt.

Time Adjustment:
5 seconds to 12 minutes.

Surge Protection:
Withstands up to 6000 volts.

Wide Sensitivity Control:
Adjustable from 100% to 30%.

Temperature Compensation:
Sensitivity adjusts automatically for consistent detection in hot and cold ambient temperatures.

Wall Switch Manual Override:
Two flip logic prevents activation by momentary power outages. Override resets to auto at dawn. No extra wiring needed.

LED Detection Indicator:
Shows when sensor is detecting in daytime and glows red at night for "on-guard" deterrence.

Advanced Detection Logic:
Minimizes false triggers.

Color Matched Lens:
Dark lens with bronze units, white lens with white units.

RF Immunity:
Circuits fully shielded for maximum radio frequency immunity.

Horizontal Lock, No-tool Joints:
Keeps sensing pattern level for fast, error-free installation.

Photoelectric Control:
Deactivates lights during daylight. Fully adjustable for 24 hour operation or custom applications.

Floodlights:
Precision die cast aluminum. 1/2" NPS threaded arm with serrated locking swivel fits all standard mounting boxes and covers.

Voltage:
120 Volts AC 60 Hertz.

Detection:
110° view.

Switching Capacity:
1000 watts incandescent @ 120 volts, 8 amps.

Patents:
RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

Warranty:
10 year sensor warranty.

Copyright ©2013 RAB Lighting, Inc. All Rights Reserved