ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

U17970K3LK2L 320A 1PH Ug 4T LVR Bypass Meter Socket

Milbank

Catalog Number	U17970K3LK2L
Manufacturer	Milbank
Description	Meter Socket, 320 A, 30 In Overall Height, 15 In Overall Width, 4-7/8 In Overall Length, Surface Mount, 1 Phase, Plain Top Hub, 4 Jaws, 4 Wires, 600 V Ac, #4 Awg to 600 Kcmil;1/0 Awg to 250 Kcmil;#6 Awg to 350 Kcmil Wire Size, Underground Feed, 32.4 LB
Weight per unit	32.4 (lbs/each)
Product Category	Residential Single Meter Socke

Features

amperage rating	320
Bypass Type	Lever Bypass
Cable Entry	Underground
cutout size	No Main Breaker
insulation	Glass Polyester
Phase	1

Dimensions and Weight

Size	4.844L x 15W x 30H

Descriptions

Also Known As...	Meter Box
	Meter Socket
Description	320A 1PH UG 4T LVR BYPASS METER SOCKET
extra long description	MILB U1797-O-K3L-K2L 320A 4T RL SWY
Long Description	Meter Socket, 320 A, 30 in Overall Height, 15 in Overall Width, 4-7/8 in Overall Length, Surface Mount, 1 Phase, Plain Top Hub, 4 Jaws, 4 Wires, 600 V ac, #4 AWG to 600 kcmil;1/0 AWG to 250 kcmil;#6 AWG to 350 kcmil Wire Size, Underground Feed, 32.4 lb

Manufacturer Information

Brand	MILBANK
GTIN	00784572301726
UPC	784572301726

Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Ringless Meter Socket

Packaging

Carton	1
Weight Per each	32.4

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	G90 Galvanized Steel with Powder Coat Finish
Frequency Rating	60
Mounting	Surface Mount
standard	UL Listed;Type 3R