ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

URD21000 Urd 2-2-4 Stephens Alu 1000'

King Wire Inc.

Catalog Number	URD21000
Manufacturer	King Wire Inc.
Description	Underground Distribution Cable, Stranded, 165 A/120 A, 600 V, 7 Strands, 3 Conductors, #2 Awg Conductor Size, 1000 FT Overall Length, 870 Mil Outside Diameter, 80 Mil (Phase/Neutral) Insulation Thickness, Aluminum Conductor Material, Polyethylene (Xlpe) Insulation Material, Yellow (Extruded Stripe), +90 °C Operating Temperature, 249 LB/1000 FT
Weight per unit	0.2620 (lbs/ft)
Product Category	Rwu

Features

Shielding Type	Non-Shielded
Stranding	7 STRANDS

Material, Color, and Finish

Color Code	Yellow Extruded Stripe

Dimensions and Weight

Length	1000 ft
Outer Diameter	870 MIL

Descriptions

Commodity Description	ALUMINUM DIRECT BURIAL WIRE-RWU
Description	URD 2-2-4 STEPHENS ALU 1000'
extra long description	DIRECT BURIAL TYPE; 1000 FT; 870 MIL OUTER DIAMETER; ALUMINUM CONDUCTOR MATERIAL; UL 854 APPROVAL; 600 V VOLTAGE RATING; 165 AMPERE DIRECT BURIAL, 120 AMPERE IN DUCT CURRENT RATING; 90 DEG C TEMPERATURE RATING; 249 LB/1000 FT WEIGHT; 3 CONDUCTOR(S); XLPE INSULATION MATERIAL; 2 AWG CONDUCTOR SIZE; YELLOW EXTRUDED STRIPE COLOR CODE; REEL PACKAGE TYPE; 7 STRANDS STRANDING; NON-SHIELDED SHIELDING TYPE; TYPE CODE TRIPLEX; TRADE NAME STEPHENS; NEUTRAL CONDUCTOR SIZE 4 AWG; INSULATION THICKNESS 80 MIL (PHASE/NEUT

Taxonomies, Classifications, and Categories

Category Description	Direct Burial Wire
Type	DIRECT BURIAL

Availability

minimum qty	1000

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1000
Weight Per foot	0.262

Uses, Certifications, and Standards

Approval	UL 854
Temperature Rating	90 DEG C