ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
555 E. 15th Street
Fayetteville, AR 72701-0000
Phone: 4794434948
Fax: 4794436465



WPBD33 WEATHER PROOF DEEP BOX 1G 3 HOLE 3/4

PASS & SEYMOUR/LEGRAND

Catalog Number	WPBD33
Manufacturer	PASS & SEYMOUR/LEGRAND
Description	Weatherproof Gang Box, Powder Paint, Gray, 23 cu.in Capacity, 1 Gang, Rectangular, Knockout Cable Entry, 3/4 in Knockout Size, 3 Knockouts, Plug Mount;Lug Mount, 1 outlet, 4.59 in Length, 2.82 in Width, 2.75 in Height, 0.91 lb/EA
Weight per unit	0.9144 (lbs/each)
Product Category	Outlet Boxes, Etc. - Steel

Features

Box Depth	Deep
Cable Entry	Back, Top, Bottom
Material	Die-Cast Aluminum
Mounting Type	Screw Mount
Number Of Knockouts	3.0
Number Of Outlets	1.0
Indoor/Outdoor	Both
Number Of Outlet	1

Material, Color, and Finish

Color	Gray

Dimensions and Weight

Size	4.59 x 2.82 x 2.75

Descriptions

Construction	23
Description	WEATHER PROOF DEEP BOX 1G 3 HOLE 3/4
Features	Deep, Corrosion Resistant, Weatherproof
	Weatherproof 1 Gang Deep Box, 3 Hole 3/4, 23Cu.In. with Threaded Holes,Gray (1 Hole Each Side, 1 hole in Back)
Long Description	Weatherproof 1 Gang Deep Box, 3 Hole 3/4, 23Cu.In. with Threaded Holes,Gray (1 Hole Each Side, 1 hole in Back)
Product Type	WP Deep Box 1G 3 Hole 3/4
Extra Long Description	PAS WPBD33 WP DEEP BOX 1G 3 HOLE 3/

Manufacturer Information

Brand	Pass and Seymour
	LEGRAND-PASS & SEYMOUR
GTIN	00785007116007
UPC	785007

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
555 E. 15th Street
Fayetteville, AR 72701-0000
Phone: 4794434948
Fax: 4794436465

Taxonomies, Classifications, and Categories

Category Description	WEATHERPROOF BOXES & COVERS
Type	Weatherproof

Packaging

Carton	1
Package	8
Weight Per Each	0.9144 (lbs/each)

Uses, Certifications, and Standards

Application	3 Hole 3/4" (1 Hole Each End, 1 Hole Back)
Standard	CSA, UL, UL Listed, CSA

Pass and Seymour
Weatherproof One Gang Deep Box, Gray
Part No. WPBD33



Weatherproof 1 Gang Deep Box, 3 Hole 3/4, 23Cu.In. with Threaded Holes,Gray (1 Hole Each Side, 1 hole in Back)

Features & Benefits

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

UL listed for wet and/or damp locations with appropriate cover.

Will accept standard three-gang weatherproof covers.

Heavy die-cast aluminum.

4 closure plugs and mounting lugs furnished with all boxes.

Designed for both interior and exterior applications.

Simply strike desired knockout studs with a sharp hammer blow for clean mounting holes.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007116007	Country Of Origin	India
Material	Die-Cast Aluminum	Features	Corrosion Resistant, Deep, Weatherproof
Number of Knockouts	3	Application Sector	Commercial, Residential
Standard	UL Listed, CSA	Warranty Type	1-Year Limited Warranty
Type	Weatherproof		

Dimensions

Product Width US	2.82 in	Product Depth US	2.75 in
Product Height US	4.59 in	Cubic Capacity	23 in^3

Box Depth	Deep

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695

Technical Information

Number of Gangs	1	Size of Threaded Openings	3/4 in
Indoor/Outdoor	Both	Cable Entry	Back, Bottom, Top
Box Shape	Rectangular	Mounting Type	Screw Mount