



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CIRS Led Single Head Remote Lamp Head

Hubbell Lighting, Inc.

Catalog Number	CIRS
Manufacturer	Hubbell Lighting, Inc.
Description	N/A, Mounting Type: Wall, Ceiling, End Mount, Face Style: Universal Single/Double Face, Wording On Sign: Exit, Letter Color: Red, Color: White, Number Of Lamps: 0, Operation: Emergency Operation, Battery Type: Lead-Calcium, Battery Runtime: 90 Min, Voltage Rating: 120/277 Vac.
Weight per unit	8.3 (lbs/each)
Product Category	Exit Signs

Features

battery	Lead-Calcium
Fixture Type	Exit Sign
Lamp Type	none
Lamp Wattage	4.5
Number of Lamps	0
Voltage Rating	120/277
Wattage	4.5

Material, Color, and Finish

Color	White
housing color	White
Letter Color	RED

Dimensions and Weight

Size	12.5000 in x 2.6250 in x 10.7500 in
------	-------------------------------------

Descriptions

Description	LED SINGLE HEAD REMOTE LAMP HEAD
extra long description	DUAL HCXURW-0-RC12 HCX EXIT W/O LMP
Long Description	N/A, Mounting Type: Wall, ceiling, end mount, Face style: Universal Single/Double Face, Wording On Sign: EXIT, Letter Color: Red, Color: White, Number of Lamps: 0, Operation: emergency operation, Battery Type: Lead-Calcium, Battery Runtime: 90 min, Voltage Rating: 120/277 VAC.
Product Type	HCX Exit W/O LMP Heads Red Led Unv WH

Manufacturer Information

Brand	DUAL-LITE
GTIN	00782520862022
Manufacturers Part Number	HCXURW-0-RC12
UPC	782520862022



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
Type	Exit Sign

Packaging

Carton	1
Weight Per each	8.3

Uses, Certifications, and Standards

Application	Manufacturing; Warehouse; Offices; Hospitality; Quick Service Restaurants; Retail; Automotive Dealers; Educational; Healthcare
Mounting standard	Wall, ceiling, end mount UL 924 Listed