



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CL125 Type CL BRKR 25A/1POLE 120/240V 10K-Classified 1" *Eaton Corp*

Catalog Number	CL125
Manufacturer	Eaton Corp
Description	Eaton Classified 1" Thermal Magnetic Circuit Breaker, Type CL 1-Inch Classified Replacement Breaker, 25 A, 10 Kaic, Single-Pole, 120/240V, CL, #14-4 Awg Cu/Al, CL, Type CH Loadcenters
Weight per unit	0.3000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

### Features

dimensions	3.0000 IN X 1.0000 IN X 3.0000 IN
interrupt rating	10
Poles	1
Voltage Rating	120/240 V

### Descriptions

Description	TYPE CL BRKR 25A/1POLE 120/240V 10K-CLASSIFIED 1"
extra long description	ETN CL125 CL bkr 25A/1Pole 120/240V
Features	Eaton UL classified replacement circuit breakers are available in both 3/4-inch Type CHQ and 1-inch Type CL, single- and two-pole configurations. These breakers are classified as direct replacements by Underwriters Laboratories. In addition to a UL listing, they also come with a 15-year warranty.
Long Description	Eaton Classified 1" thermal magnetic circuit breaker, Type CL 1-Inch classified replacement breaker, 25 A, 10 kAIC, single-pole, 120/240V, CL, #14-4 AWG Cu/Al, CL, Type CH loadcenters
Product Type	CL BKR 25A/1POLE 120/240V 10K

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786676011563
Manufacturers Part Number	CL125
UPC	786676011563

### Taxonomies, Classifications, and Categories

Category Description	CLASSIFIED BREAKERS
Type	1" Thermal magnetic circuit breakers

### Packaging

Carton	1
Package	10
Weight Per each	0.3



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional EnergyOtherGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489