



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG134087FNC21C DG1 480V FR4 N1 60HP 87A CT 75HP 105A VT

Eaton Corp

Catalog Number	DG134087FNC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 380-500V Input 45 KW 60 HP CT 3PH 50/60 HZ 87A Output IP21/Type 1 Enclosure FR5 LCD Internal Emc Filter and DC Choke Ethernet, RS-485, Bacnet MS/TP, Modbus TCP and Rtu Ports 2 Exp Slots
Weight per unit	77.2 (lbs/each)
Product Category	Ac Drives

Features

dimensions	27.5000 IN X 17.0000 IN X 15.0000 IN
display	LCD graphical
Input Voltage	400 V, 380-500 V(-15%, +10%)
keypad	Included
Number of Phases	Three-phase in, three-phase out

Descriptions

Description	DG1 480V FR4 N1 60HP 87A CT 75HP 105A VT
extra long description	ETN DG1-34087FN-C21C DG1,480V FR4 ,
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 380-500V input 45 kW 60 Hp CT 3PH 50/60 Hz 87A output IP21/type 1 enclosure FR5 LCD Internal EMC filter and DC choke EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU ports 2 exp slots
Product Type	DG1, 480V FR4 , N1, 60HP, 87A/75HP, 105A VT

Manufacturer Information

Brand	Eaton
GTIN	00786685878874
Manufacturers Part Number	DG1-34087FN-C21C
UPC	786685878874

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable Frequency Drive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	77.16

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure	IP21/type 1 enclosure
standard	UL Listed,EN 61800-3,EN ISO 13849-1,EN 61800-5-1,UL 508C,cUL Listed,IEC 61508,EN 62061,RoHS Compliant,CE Marked,GoST-R,C-Tick Compliant