



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH221FRK 30A/2P HD Fusible Safety Switch 240V Nema 3R

Eaton Corp

Catalog Number	DH221FRK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, Enhanced Visible Blade, 30 A, Nema 3R, Painted Galvanized Steel, Class H, Fusible Without Neutral, Two-Pole, Two-Wire, 240 V, Max HP: 1.5, 5 HP (1PH @240V/250 VDC), #14-#2 Cu/Al
Weight per unit	19.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	30A
dimensions	18.0000 IN X 9.5000 IN X 7.5000 IN
Material	Painted galvanized steel
media	Yes
Poles	Two-pole
Voltage Rating	240V

Dimensions and Weight

Depth	18.0000
Height	7.5000
Width	9.5000

Descriptions

Description	30A/2P HD FUSIBLE SAFETY SWITCH 240V NEMA 3R
extra long description	ETN DH221FRK 30A/2P HD Fusible Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, 30 A, NEMA 3R, Painted galvanized steel, Class H, Fusible without neutral, Two-pole, Two-wire, 240 V, Max Hp: 1.5, 5 hp (1PH @240V/250 Vdc), #14-#2 Cu/Al
Product Type	30A/2P HD Fusible Sfty SW 240V N3R
Special Features	Enhanced visible blade

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685176741
Manufacturers Part Number	DH221FRK
UPC	786685176741



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch

Packaging

Carton	1
Weight Per each	19

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	Nema 3R
standard	UL Listed