



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS6375 LKG "LT, 50A 125/250V, 3P4W *Hubbell Wiring Devices*

Catalog Number	CS6375
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A, 125V/250V Ac, 3-Pole 4-Wire Grounding, Non-Nema, Screw Terminal, Steel
Weight per unit	0.8500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	50
connection	Pressure Screw Terminals
Current Rating	50
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	4-Wire
pallet quantity	810
Phase	1
Poles	3-Pole
Voltage Rating	125/250 VAC
Wattage	12,500
Wire Size	#10 to #6

Dimensions and Weight

Size	2.17 in x 3.50 in x 2.62 in
------	-----------------------------

Descriptions

Description	LKG "LT, 50A 125/250V, 3P4W
extra long description	HWDK CS6375 LKG INLT, 50A 125/250V,
Features	Hubbell's 50 Amp Twist-Lock® Devices feature a heavy-duty design and super-tough nylon housing built for heavy-duty applications and impact resistance, even in the harshest environments. Their rigid construction restricts contact distortion, minimizing the possibility of mating dissimilar devices. The cord grip's offset gripping jaws securely hold the conductors and the cord jacket for excellent strain relief.
Long Description	Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A, 125V/250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Steel
Product Type	LKG Inlt, 50A 125/250V, 3P4W
Special Features	Standard Product



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585828206
Manufacturers Part Number	CS6375
UPC	783585828206

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Flanged Inlet

Packaging

Carton	1
Package	10
Weight Per each	0.85

Uses, Certifications, and Standards

Application	Extra Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	Non-NEMA
standard	Certified to CSA C22.2 No.42;Listed to UL 498