

Specifications



Eaton DH361UDK

Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 30 A, NEMA 12, Painted galvanized steel, Non-Fusible, Three-pole, Three-wire, 3 at 240 Vac TD 1 Ph, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 10 at 240 Vac TD 3 Ph

General specifications

| | |
|----------------------|--|
| PRODUCT NAME | Eaton heavy duty non-fusible safety switch |
| CATALOG NUMBER | DH361UDK |
| UPC | 782113205601 |
| PRODUCT LENGTH/DEPTH | 10.22 in |
| PRODUCT HEIGHT | 14.14 in |
| PRODUCT WIDTH | 8.76 in |
| PRODUCT WEIGHT | 17 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | NEC 230.62 (C) Compliant Barrier |
| CERTIFICATIONS | UL Listed |
| CATALOG NOTES | Suitable for service entrance use with a neutral or ground lug kit installed. Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened. |

| Physical Attributes | |
|---------------------|--------------------------|
| ENCLOSURE | NEMA 12 |
| ENCLOSURE MATERIAL | Painted galvanized steel |
| FUSE CONFIGURATION | Non-fusible |
| NUMBER OF POLES | Three-pole |
| NUMBER OF WIRES | 3 |
| TYPE | Single-throw |

| Performance Ratings | |
|---------------------|--|
| AMPERAGE RATING | 30A |
| HP RATING - MAX | 3 at 240 Vac TD 1 Ph, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 10 at 240 Vac TD 3 Ph, 20 at 480 Vac TD 3 Ph, 30 at 600 Vac TD 3 Ph, 5 at 250 Vdc |
| NEMA RATING | NEMA 12, NEMA 3R |
| VOLTAGE RATING | 600 V |

| Miscellaneous | |
|------------------|-------------------------|
| PRODUCT CATEGORY | Heavy Duty, Non-Fusible |

| Resources | |
|-------------------------------|---|
| CATALOGS | Commercial Distribution, Switching Devices, Volume 2, Tab 1 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - DH361UDK |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

