



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **E22NB3 III. Pushbutton-Flush 4X** *Eaton Corp*

Catalog Number	E22NB3
Manufacturer	Eaton Corp
Description	Eaton E22 Pushbutton, 22.5 MM, Non-Metallic Heavy-Duty, 25 MM, Nema 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Green Actuator, Flush, Plastic, No Light Unit, Black Bezel
Weight per unit	0.0800 (lbs/each)
Product Category	Push Button Components

### **Features**

action	Green
actuator	Flush

### **Dimensions and Weight**

Depth	1.5
Height	0.5
Size	25 mm
Width	1.5

### **Descriptions**

Description	ILL. PUSHBUTTON-FLUSH 4X
extra long description	ETN E22NB3 ILL. PUSHBUTTON-FLUSH 4X
Features	Eaton's 22.5 mm industrial heavy-duty pushbutton line offers a wide array of functional, smartly styled illuminated and non-illuminated pushbuttons, selector switches, push-pulls, action and twist-to- release operators. The complete line also includes transformer, full voltage, resistor, LED or neon light units.
Long Description	Eaton E22 Pushbutton, 22.5 mm, Non-metallic Heavy-Duty, 25 mm, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Green actuator, Flush, Plastic, No light unit, Black bezel
Product Type	III. Pushbutton-Flush 4X

### **Manufacturer Information**

Brand	EATON CUTLER-HAMMER
GTIN	00782113468280
Manufacturers Part Number	E22NB3
Model	Pushbutton
UPC	782113468280

### **Taxonomies, Classifications, and Categories**

Category Description	MINATURE PILOT DEVICES.22MM
----------------------	-----------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.08

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	CSA Certified, IEC 947-5-1 MTTA, Lloyd's Register Certified, UL 508, CE Marked