

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



EZ20SNW Ez 20 Cu-In. 1G Nail On | Knock Outs Cantex, Inc

UPC

Catalog Number	EZ20SNW
Manufacturer	Cantex, Inc
Description	Cantex EZ20SNW Ez Box Is A 20.3 Cu. In. 1-Gang Electrical Switch and Outlet Box For Residential or Light Commercial Electrical Installations. It Features Knockouts and Enhanced Angled Nails For Easy Installation.
Weight per unit	0.2000 (lbs/each)
Product Category	Boxes & Covers
Features	
Cable Entry	4 knockouts
Knockouts	4
Material	PVC
Mounting Type	Nail-On
Number of Gangs	1
Material, Color, and Finish	
Color	Gray
Dimensions and Weight Size	Non-Applicable
Descriptions	
Construction	new work
Description	1G WALL BOX - NAIL ON
extra long description	CTX EZ20SNW 20 CU IN SINGLE W/NAILS
Features	CANTEX EZ20SNW EZ BOX is a 20.3 cu. in. 1-gang electrical switch
	and outlet box for residential or light commercial electrical installations. It features knockouts and enhanced angled nails for easy installation.
Long Description	CANTEX EZ20SNW EZ BOX is a 20.3 cu. in. 1-gang electrical switch and outlet box for residential or light commercial electrical installations. It features knockouts and enhanced angled nails for
D II.T.	easy installation.
Product Type	20 Cu In Single W/Nails/Ko
Special Features	enhanced angled nails
Manufacturer Information	
Brand	PVC & Accessories
GTIN	00088700970854
Manufacturers Part Number	EZ20SNW

088700970854



ELLIOTT ELECTRIC SUPPLY 2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941

We Deliver...Lower Cost, Quality Products, & Personal Service

Fax: 936-560-4685

Taxonomies, Classifications, an	nd Categories
Category Description	· · · · · · · · · · · · · · · · · · ·
Туре	1-gang switch and outlet box
Packaging	
Carton	100
Weight Per each	0.2
Uses Certifications and Stand	ards

uses, certifications, and Standards	
Application	1-gang switch and outlet box
Mounting	Nail-On
standard	ETL, 2-Hour Fire Rated