



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FB2PST120R Red Warning Light 120V MT STR

Federal Signal Corp.

Catalog Number	FB2PST120R
Manufacturer	Federal Signal Corp.
Description	Fireball Strobe Warning Light, 120VAC, Red - Available In 12-24VDC, 24VDC, 120VAC and 240VAC. Six Lens Colors: Amber, Blue, Clear, Green, Magenta and Red. 10, 000 Hour Strobe Tube. Integrated 1/2-Inch NPT Pipe and Surface Mount. Indoor/Outdoor Use. Conformal Coated PCB. Type 4X, IP66 Enclosure. IP69K Compliant. Csa Certified. UI and Cul Listed.
Weight per unit	2.1 (lbs/each)
Product Category	Bells, Horns, Sirens, BZZRS, S

Features

amperage rating	0.25
average life	10,000
Light Source	Strobe Tube
Material	Zinc/Polycarbonate
Shape	Cylindrical
Voltage Rating	120VAC 50-60Hz

Material, Color, and Finish

Color	Red
Style	Strobe

Dimensions and Weight

Size	5.25 H x 4.10 W x 4.10 D
------	--------------------------

Descriptions

Description	RED WARNING LIGHT 120V MT STR
extra long description	FED-SIG FB2PST-120R STROBE 120VAC P
Long Description	Fireball Strobe Warning Light, 120VAC, Red - Available in 12-24VDC, 24VDC, 120VAC and 240VAC. Six lens colors: Amber, Blue, Clear, Green, Magenta and Red. 10,000 hour strobe tube. Integrated 1/2-inch NPT pipe and surface mount. Indoor/outdoor use. Conformal coated PCB. Type 4X, IP66 enclosure. IP69K compliant. CSA Certified. UL and cUL Listed.
Product Type	Strobe 120VAC Pipe-Surface Mount Red
Special Features	Type 4X, IP66 Enclosure

Manufacturer Information

Brand	Federal Signal
GTIN	00782979900504
Manufacturers Part Number	FB2PST-120R
Model	FB2PST
UPC	782979900504



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	RADIOS
Type	Strobe Warning Light

Packaging

Carton	1
Weight Per each	2.12

Uses, Certifications, and Standards

Application	Indoor/Outdoor
environmental conditions	-31 to 150
Mounting	1/2-Inch NPT Pipe/Surface
nema rating	Type 4X, IP66, IP69K Enclosure
standard	UL Listed/cUL Listed/CSA Certified