



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **GAR2226 4SLD-2/0STR Awg MCHNL Ground Conn** *Burndy LLC*

Catalog Number	GAR2226
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 Awg (Sol)-2/0 Awg (STR), 4" Pipe, 4"-4-1/2" Rod, Bright Dipped.
Weight per unit	2.4 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Bolt Size	3/8
Material	COPPER ALLOY

### **Material, Color, and Finish**

Finish	Dip Coat-Primed/Powder-Coated/Textured Paint
--------	--

### **Descriptions**

Description	4SLD-2/0STR AWG MCHNL GROUND CONN
extra long description	BUR GAR2226 4-2/0CU 4IPS
Long Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)-2/0 AWG (Str), 4" Pipe, 4"-4-1/2" Rod, Bright Dipped.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Ground Rod Size: 4 - 4-1/2 IN, Tube (ips) Size: 4 IN, Installation Torque: 240 IN-LB, Height: 6-3/8 IN, Width: 5-7/8 IN

### **Manufacturer Information**

Brand	Burndy Canada
GTIN	00781810237403
Manufacturers Part Number	GAR2226
sub brand	DURIMUM
UPC	781810237403

### **Taxonomies, Classifications, and Categories**

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GAR



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	2.41

## Uses, Certifications, and Standards

Application	For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post
standard	UL467