



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GBB10R 10A 250VAC/125VDC Vfa 1/4X1-1/4" Rohs Fuse

Bussmann Fuses

| | |
|------------------|--|
| Catalog Number | GBB10R |
| Manufacturer | Bussmann Fuses |
| Description | Eaton GBB Series Very Fast-Acting Fuse, 20A, 250 Vac, 125 VDC, R |
| Weight per unit | 0.0050 (lbs/each) |
| Product Category | Small Dimension Fuses |

Features

| | |
|--------------------|--|
| amperage rating | 10 A |
| connection | Ferrule End X Ferrule End |
| dimensions | 1.2500 IN X 0.2500 IN X 0.2500 IN |
| interrupt rating | 10 kAIC at 125 Vac/dc200 AIC at 250 Vac |
| Material | Nickel-plated brass end cap constructionCeramic tube |
| Response Time | 2 min at 150%, 1 sec at 250% |
| type of indicators | Non-Indicating |
| Voltage Rating | 250 VAC, 125 VDC |

Dimensions and Weight

| | |
|------|-----------------------------------|
| Size | 1/4 In Diameter X 1-1/4 In Length |
|------|-----------------------------------|

Descriptions

| | |
|------------------------|--|
| Description | 10A 250VAC/125VDC VFA 1/4X1-1/4" ROHS FUSE |
| extra long description | BUSS GBB-10-R GBB 10A BUSS FA 5-IN |
| Features | Very fast-acting, ceramic tube 1/4" x 1-1/4" ferrule fuse designed to UL 248-14 for overcurrent protection of sensitive electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip or purchase with available axial leads for thru-hole installation. Eaton's GBB very fast-acting, ceramic tube 1/4" x 1-1/4" ferrule fuses are designed to UL 248-14 for overcurrent protection of sensitive electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, b |
| Long Description | Eaton GBB Series Very fast-acting fuse, 20A, 250 Vac, 125 Vdc, R |
| Product Type | GBB 10A Buss Fa 5-In Box -R |
| Special Features | Interrupt Rating 200 Amp at 250 Vac, 10000 Amp at 125 Vac/Vdc, Material Ceramic Tube, Nickel Plated Brass Endcap, ROHS Compliant |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | Eaton Bussmann series |
| GTIN | 00051712549882 |
| Manufacturers Part Number | GBB-10-R |
| UPC | 051712549882 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | GLASS FUSES (and ceramic) |
| Type | Very fast-acting fuse |

Availability

| | |
|-------------|---|
| minimum qty | 5 |
|-------------|---|

Packaging

| | |
|-----------------|-------|
| Carton | 5 |
| Weight Per each | 0.005 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Ind Facilities & Factories - Facility: Safety and Security Systems |
| standard | CE Marked,RoHS Compliant |