



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GLS10 4" Ground Bushing *Crouse-Hinds*

Catalog Number	GLS10
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series GLS Grounding Bushing, Rigid/Imc, Aluminum Lug, #3/0-6 Awg, Malleable Iron, 105°C, Threadless, 4"
Weight per unit	1.1 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Set Screw
dimensions	5.9000 IN X 2.9000 IN X 7.8000 IN
Material	Malleable Iron Body, Plastic Throat Liner

### Dimensions and Weight

Size	4 in
------	------

### Descriptions

Description	4" GROUND BUSHING
extra long description	MIDWEST GLS10 4 GRND BUSH 105C INSU
Features	Crouse-Hinds series grounding bushings are used with threaded and threadless rigid/IMC conduit to provide a means of grounding conduit through an insulated bushing.
Long Description	Eaton Crouse-Hinds series GLS grounding bushing, Rigid/IMC, Aluminum lug, #3/0-6 AWG, Malleable iron, 105°C, Threadless, 4"
Product Type	4 GRND Bush 105C Insul 3 to 6 Al Lug
Special Features	With 6 To 3/0 AWG Aluminum Lug for Copper/Aluminum Grounding Conductor, Weight 110 Lb per 100

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564112484
Manufacturers Part Number	GLS10
UPC	784564112484

### Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	Grounding bushing

### Packaging

Carton	1
Weight Per each	1.05



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /  
Institutional Buildings / Structures - Other

standard

UL, CSA

Temperature Rating

105 DEG C