

# Specifications

Photo is representative

## Eaton HM25030-3CR

Eaton Bussmann series HM modular fuse block, CR, 0-30 A, Three-pole, Class K, Class H, 10 kAIC, 250 V

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series HM modular fuse block
<b>CATALOG NUMBER</b>	HM25030-3CR
<b>UPC</b>	051712511179
<b>PRODUCT LENGTH/DEPTH</b>	3.16 in
<b>PRODUCT HEIGHT</b>	1.3 in
<b>PRODUCT WIDTH</b>	2.88 in
<b>PRODUCT WEIGHT</b>	0.27 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	Contact Manufacturer UL Listed CSA Certified

## Electrical rating

**AMPERAGE RATING** 0-30A

**SHORT-CIRCUIT RATING** 10 kA

**VOLTAGE RATING** 250 V

## General information

**CLASS** Class H  
Class K

**SPECIAL FEATURES** CR

## Physical details

**NUMBER OF POLES** Three-pole

## Resources

**CATALOGS** [HM25030-3CR~Fuse Block, Class H, 250V 30A, 3 Pole](#)

[Bussmann series complete full line catalog no. 1007](#)

**CERTIFICATION REPORTS** [Eaton Bussmann EU Declaration of conformity 93-68-EEC2204](#)

[Bussmann series Fuseology](#)

**MULTIMEDIA** [Class H\(K\), J and R Power distribution fuse block overview](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - HM25030-3CR](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

Photo is representative

## Eaton HM25030-3CR

Eaton Bussmann series HM modular fuse block, CR, 0-30 A, Three-pole, Class K, Class H, 10 kAIC, 250 V

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series HM modular fuse block
<b>CATALOG NUMBER</b>	HM25030-3CR
<b>UPC</b>	051712511179
<b>PRODUCT LENGTH/DEPTH</b>	3.16 in
<b>PRODUCT HEIGHT</b>	1.3 in
<b>PRODUCT WIDTH</b>	2.88 in
<b>PRODUCT WEIGHT</b>	0.27 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	Contact Manufacturer UL Listed CSA Certified

## Electrical rating

**AMPERAGE RATING** 0-30A

**SHORT-CIRCUIT RATING** 10 kA

**VOLTAGE RATING** 250 V

## General information

**CLASS** Class H  
Class K

**SPECIAL FEATURES** CR

## Physical details

**NUMBER OF POLES** Three-pole

## Resources

**CATALOGS** [HM25030-3CR~Fuse Block, Class H, 250V 30A, 3 Pole](#)

[Bussmann series complete full line catalog no. 1007](#)

**CERTIFICATION REPORTS** [Eaton Bussmann EU Declaration of conformity 93-68-EEC2204](#)

[Bussmann series Fuseology](#)

**MULTIMEDIA** [Class H\(K\), J and R Power distribution fuse block overview](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - HM25030-3CR](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

