



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GX2929 2/0-250 Cop Ground Conn *Burndy LLC*

Catalog Number	GX2929
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable Cross Connection, 2/0 Awg (Sol.) - 250 Kcmil (Run), 2/0 Awg (Sol.) - 250 Kcmil (Tap), 3/8" Stud.
Weight per unit	0.6200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	COPPER ALLOY
----------	--------------

Descriptions

Description	2/0-250 COP GROUND CONN
extra long description	BUR GX2929 2/0-250 TO 2/0-250 X CON
Long Description	Mechanical Grounding Connector, Cable Cross Connection, 2/0 AWG (Sol.) - 250 kcmil (Run), 2/0 AWG (Sol.) - 250 kcmil (Tap), 3/8" Stud.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Cross Connecting A Wide Range Of Cable, The High Copper Alloy Cast Body, DURIUM U-Bolts, Nuts, And Lockwashers Make The GX Suitable For Burial In Soil Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Installation Torque: 240 IN-LB, Length: 1-7/8 IN, Height: 2-3/4 IN, Width: 1-7/8 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810260692
Manufacturers Part Number	GX2929
sub brand	Mechanical Connector
UPC	781810260692

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GX

Packaging

Carton	1
Package	50
Weight Per each	0.62



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Cross Connecting A Wide Range Of Copper Cable, Direct
Burial In Earth Or Concrete

standard

UL467