



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IOPA4P32N35I 4LT T8 Bal *Advance By Signify*

Catalog Number	IOPA4P32N35I
Manufacturer	Advance By Signify
Description	The Right Choice For A Broad Range Of New Construction and Retrofit Applications Compatible With Energy Saving Lamps;Eligible For Utility Rebates;Maximizes Fixture Design;Reduces Packaging Waste Reliable and Energy Efficient Philips Advance'S Centium Commercial Grade Specifications, Plus Added Benefits Of Lamp Striation Reduction Technology. Intellivolt (120-277V) Input Voltage Range;Lamp Striation Reduction;Meets Nema Premium/Cee;Smallest Enclosure In Industry General Office Lighting, Institutional, Gover
Weight per unit	0.8000 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

Ballast Factor	0.87
Lamp Type	T8
Number of Lamps	4
Power Factor	0.98
start type	Instant Start
total harmonic distortion	10
Voltage Rating	120-277
Wattage	32
Wire Type	SOLID

Material, Color, and Finish

Housing Material	Metal
------------------	-------

Dimensions and Weight

Height	3.94
Width	5.12



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	4LT T8 BAL
extra long description	ADV 498857 ELE BALLAST (4) F32T8 12
Long Description	The right choice for a broad range of new construction and retrofit applications Compatible with Energy Saving lamps;Eligible for Utility Rebates;Maximizes fixture design;Reduces packaging waste Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology. IntelliVolt (120-277V) input voltage range;Lamp Striation Reduction;Meets NEMA Premium/CEE;Smallest enclosure in industry General office lighting, institutional, gover
Product Type	Ele Ballast (4) F32T8 120-277V
Special Features	UL, CSA, NEMA Premium, RoHS

Manufacturer Information

Brand	Signify Electronics
GTIN	00781087115244
Manufacturers Part Number	498857
UPC	781087115244

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Electronic Fluorescent

Packaging

Carton	1
Package	10
Weight Per each	0.8

Uses, Certifications, and Standards

Frequency Rating	50to60
standard	CSA certificate;UL certificate;CEC Listing;CEE Rated;NEMA Premium;RoHS Compliant