



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED14ET8G4850 14W Led T8 48" 50K Type A 2050LM 80cri

*Ge By Current Lamps*

Catalog Number	LED14ET8G4850
Manufacturer	Ge By Current Lamps
Description	Linear Fluorescent Led Lamp, Non-Dimmable, Integrated Type; 48 Inch; UL, DLC Approval; Damp Location Application; 14 Watt Wattage; Led Tube; G13 Base Type; 50000 Life In Hour; T8 Shape Designation; 2050 Lumen Intensity; 5000; 80 Color Rendering Index
Weight per unit	0.5380 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Intensity	2050 Lumen
Item	LED Tube
Wattage	14 Watt

### Material, Color, and Finish

Base Type	G13
Color Rendering Index	80 A
Color Temperature in Kelvin	5000

### Dimensions and Weight

Length	48 INCH
--------	---------

### Descriptions

Additional Information	Ballast Type Instant Start or Program Start
Commodity Description	Led Linear Fluorescent Straight, U-Shape & Circular Lamps
Description	14W LED T8 48" 50K TYPE A 2050LM 80CRI
extra long description	NON-DIMMABLE, INTEGRATED TYPE; 48 INCH; UL, DLC APPROVAL; DAMP LOCATION APPLICATION; 14 WATT WATTAGE; LED TUBE; G13 BASE TYPE; 50000 LIFE IN HOUR; T8 SHAPE DESIGNATION; 2050 LUMEN INTENSITY; 5000; 80 COLOR RENDERING INDEX; BALLAST TYPE INSTANT START OR PROGRAM START
Long Description	LINEAR FLUORESCENT LED LAMP, NON-DIMMABLE, INTEGRATED TYPE; 48 INCH; UL, DLC APPROVAL; DAMP LOCATION APPLICATION; 14 WATT WATTAGE; LED TUBE; G13 BASE TYPE; 50000 LIFE IN HOUR; T8 SHAPE DESIGNATION; 2050 LUMEN INTENSITY; 5000; 80 COLOR RENDERING INDEX
Product Type	Linear Fluorescent Led Lamp



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	GE LIGHTING, INC./LAMPS
GTIN	10043168343005
Manufacturers Part Number	LED14ET8G4850
UPC	043168343008

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Non-Dimmable, Integrated

## Packaging

Carton	1
Package	20
Weight Per each	0.538

## Uses, Certifications, and Standards

Application	Damp Location
Approval	UL, DLC