



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22SDRPRK01 MTN Mushroom PB Red 1NC *Eaton Corp*

Catalog Number	M22SDRPRK01
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, M22 Pushbutton, Complete Device, 22.5 MM, Knob, Mushroom , Maintained, Non-Illuminated, Bezel: Black, Button: Red, 1NC, IP66, Nema 4X, 13
Weight per unit	0.0700 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

actuator	Mushroom
Contact Configuration	1 NC
dimensions	4.0000 IN X 5.0000 IN X 1.5000 IN
operating cycles	1 million

Dimensions and Weight

Depth	4.0000
Height	1.5000
Size	22.5 mm
Width	5.0000

Descriptions

Description	MTN MUSHROOM PB RED 1NC
extra long description	ETN M22S-DRP-R-K01 MTN MUSHROOM PB
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, M22 Pushbutton, Complete Device, 22.5 mm, Knob, Mushroom , Maintained, Non-illuminated, Bezel: Black, Button: Red, 1NC, IP66, NEMA 4X, 13
Product Type	MTN Mushroom PB Red 1NC



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00786685282633
Manufacturers Part Number	M22S-DRP-R-K01
Model	Modular pushbutton
UPC	786685282633

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
Type	Modular pushbutton

Packaging

Carton	1
Weight Per each	0.07

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
environmental conditions	IP67, IP69K
standard	Lloyd's Register Certified,CCC Marked,CSA Certified,GoST-R,CE Marked,Bureau Veritas