

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy 75701-0000, TX Tyler Phone: 903-509-9882 Fax: 903-509-9832



## M22DXSWRGYB Nema 4X, 13, 5, 000, 000 Operations, 22.5 MM Eaton Corp

Catalog Number	M22DXSWRGYB
Manufacturer	Eaton Corp
Description	Eaton 22.5 MM RMQ-Titan Pushbutton, Black, Red, Green, White, Yellow, Blue Actuator, Silver Bezel, IP67, IP69K, Non-Illuminated, Flush Mounting, Nema 4X, 13, 5, 000, 000 Operations, Momentary, 22.5 MM, Flush Pushbutton, M22
Weight per unit	1.0 (lbs/each)
Product Category	Push Button Complete Assemblie
Features	
action	Black, red, green, white, yellow, blue
actuator	Flush, Button
operating cycles	5 million
Dimensions and Weight	
Depth	7
Height	1.5
Size	22.5 mm
Width	5
Descriptions	
Description	NEMA 4X, 13,5,000,000 OPERATIONS,22.5 MM
extra long description	ETN M22-D-X-SWRGYB NON-ILL MOM PB S
Features	This attractive, functional line of pushbuttons features a
	space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton 22.5 mm RMQ-Titan Pushbutton,Black, Red, Green, White Yellow, Blue Actuator,Silver bezel,IP67, IP69K,Non-illuminated,Flush mounting,NEMA 4X, 13,5,000,000 operations,Momentary,22.5 mm,Flush Pushbutton,M22
Product Type	Non-III Mom PB Sil-BZL FLSH Button 6pack
Manufacturer Information	,
Brand	Eaton
GTIN	00786685276434
Manufacturers Part Number	M22-D-X-SWRGYB
Model	Modular pushbutton
UPC	786685276434



## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy 75701-0000, TX Tyler Phone: 903-509-9882 Fax: 903-509-9832

Taxonomies, Classifications, and C Category Description	Categories PUSHBUTTONS & CHIMES
Packaging	4
Carton Weight Per each	1
Uses, Certifications, and Standard	S
Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
Mounting	FLUSH
standard	CCC Marked,Lloyd's Register Certified,CSA Certified,CE Marked.Bureau Veritas.GoST-R