



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **MMX32AA7D0N00 Mmax 3P 230V In/3P 230V Out 7.0A 2.0HP FS2 W/O Emc** *Eaton Corp*

Catalog Number	MMX32AA7D0N00
Manufacturer	Eaton Corp
Description	Eaton M-Max Series Sensorless Vector Adjustable Frequency Drive, Three-Phase In, Three-Phase Out, 7.0A, 2.0HP, 230V Input and Output Voltage, FS2, W/O Emc
Weight per unit	3.0 (lbs/each)
Product Category	Ac Drives

### Features

dimensions	5.5000 IN X 3.0000 IN X 4.5000 IN
------------	-----------------------------------

### Descriptions

Description	MMAX 3P 230V IN/3P 230V OUT 7.0A 2.0HP FS2 W/O EMC
extra long description	ETN MMX32AA7D0N0-0 MMX 3P 230V/230V
Features	Demand more simplicity. The M-Max series of variable frequency drive is a compact system with a broad power range. Factor in the conformal board coating, unique mounting characteristics, simple programming, and its 50°C Rating and the M-Max is perfectly suited for machinery applications in many industries including material handling, HVAC, pumping and more.
Long Description	Eaton M-Max Series sensorless vector adjustable frequency drive, Three-phase in, three-phase out, 7.0A, 2.0HP, 230V input and output voltage, FS2, W/O EMC
Product Type	MMX 3P 230V/230V, 7.0A, 2.0HP, FS2, W/O Emc

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685268750
Manufacturers Part Number	MMX32AA7D0N0-0
UPC	786685268750

### Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Sensorless vector adjustable frequency drive

### Packaging

Carton	1
Weight Per each	3



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies and  
OEMs - Other

standard

C-Tick Compliant,CE Marked,RoHS Compliant