

Eaton QBGFT1020

Catalog Number: QBGFT1020

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,20A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,#14–10 Cu, #12–10 Al,QBGF

General specifications



Product Name

Eaton QB GFCI circuit breaker

Catalog Number

QBGFT1020

UPC

786680130960

Product Length/Depth

1 in

Product Height

1 in

Product Width

1 in

Product Weight

0.4 lb

Warranty

1 year

Certifications

UL 489

Physical Attributes

Circuit breaker type

QBGF

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Ground fault circuit breaker

Wire size

#14-10 AWG Cu

#12-10 AWG Al

Performance Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Trip rating

5 mA trip sensitivity

Voltage rating

120/240 V

Miscellaneous

Special features

5 mA Trip Sensitivity

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - QBGFT1020](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton QBGFT1020

Catalog Number: QBGFT1020

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,20A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,#14–10 Cu, #12–10 Al,QBGF

General specifications



Product Name

Eaton QB GFCI circuit breaker

Catalog Number

QBGFT1020

UPC

786680130960

Product Length/Depth

1 in

Product Height

1 in

Product Width

1 in

Product Weight

0.4 lb

Warranty

1 year

Certifications

UL 489

Physical Attributes

Circuit breaker type

QBGF

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Ground fault circuit breaker

Wire size

#14-10 AWG Cu

#12-10 AWG Al

Performance Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Trip rating

5 mA trip sensitivity

Voltage rating

120/240 V

Miscellaneous

Special features

5 mA Trip Sensitivity

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - QBGFT1020](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia