



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

149 North Wilson St.
76028-0000, TX Burleson
Phone: 817-447-0192
Fax: 817-426-1193



S20N11S03CULS42 3KVA Encaps TX 1PH 240X480-120/240 115C

Eaton Corp

Catalog Number	S20N11S03CULS42
Manufacturer	Eaton Corp
Description	Eaton General Purpose Encapsulated Transformer, Ep, Copper, Nema 3R, 176, 60 HZ, Low Sound 42 DB, Single-Phase, 240 V, 480 V, 120/240 V, None, 115 °C Rise, 3 Kva, Indoor-Outdoor, 3a
Weight per unit	72.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

Features

design	EP
dimensions	8.0000 IN X 7.6900 IN X 14.2500 IN
kva rating	3
Number of Phases	1
Tap Size	NONE

Descriptions

Description	3KVA ENCAPS TX 1PH 240X480-120/240 115C
extra long description	ETN S20N11S03CULS42 3KVA ENCAPS TX
Features	Eaton's EP (single-phase) and EPT (three-phase) general purpose encapsulated dry-type transformers are of the two-winding type, encapsulated (potted) in a mix of epoxy coated sand and gravel, and are available in a wide variety of primary and secondary voltage combinations. General purpose encapsulated transformers are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards, and are designed for continuous operation at rated kVA.
Long Description	Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 176, 60 Hz, low sound 42 dB, single-phase, 240 V, 480 V, 120/240 V, NONE, 115 °C rise, 3 KVA, indoor-outdoor, 3A
Product Type	3KVA Encaps TX 1PH 240X480-120/240 115C

Manufacturer Information

Brand	Eaton
GTIN	00786680080791
Manufacturers Part Number	S20N11S03CULS42
UPC	786680080791

Taxonomies, Classifications, and Categories

Category Description	3 PHASE TRANSFORMERS
Type	Encapsulated transformer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

149 North Wilson St.
76028-0000, TX Burleson
Phone: 817-447-0192
Fax: 817-426-1193

Packaging

Carton	1
Weight Per each	72

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL Listed