



Extra duty
while-in-use covers
for outdoor environments

Extra Duty While-in-Use Covers



TP7488XD



TP7488XDW



TP7487XD



TP7489XD



Applications:

- Commercial and residential landscape lighting, vending machines, etc.
- Seals out moisture and sheds water, ice and snow
- Meets or exceeds outdoor low voltage requirements

Description:

- 1-gang easy-to-close cover for horizontal applications
- 1-gang easy-to-close cover for vertical applications
- 2-gang easy-to-close cover for either horizontal or vertical applications

Features:

- Meets NEC® and CEC® extra duty requirements for any application
- Rugged UV-resistant polycarbonate cover and back protects devices without cracking or breaking and is non-corrosive
- Robust design with stainless steel reinforced hinge
- Easy-to-close padlockable cover
- Box inserts accommodate decorator and GFCI devices, duplex receptacles, and a variety of single receptacle sizes and toggle switches
 - 1-gang box includes 3 inserts for 8 different configurations
 - 2-gang box includes 4 inserts for over 60 different configuration
- Cover cord opening fits #12 AWG or small gauge
- Cover depth is 3-1/4"
- Box cover includes pre-mounted gasket
- Listed for use in wet locations



Certification and Compliances:

- cULus Listed to UL514D
- UL File # E-102328
- Meets 2014 NEC® 406.9 and CEC® Rule 26-702
- NEMA 3R

Standard Materials & Finishes:

- Clear cover, body and cover plates – polycarbonate
- Gasket – ethylene vinyl acetate (EVA)
- Hinge pin – stainless steel

Extra Duty While-in-Use Weather Protective Covers

Cat. #	Gang	Mounting Description	Material	Color	Depth
TP7488XD	1	Horizontal	Polycarbonate	Gray	3-1/4"
TP7488XDW	1	Horizontal	Polycarbonate	White	3-1/4"
TP7487XD	1	Vertical	Polycarbonate	Gray	3-1/4"
TP7487XDW	1	Vertical	Polycarbonate	White	3-1/4"
TP7489XD	2	Horizontal/Vertical	Polycarbonate	Gray	3-1/4"
TP7489XDW	2	Horizontal/Vertical	Polycarbonate	White	3-1/4"

Color Information



Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2015 Eaton
All Rights Reserved
Printed in USA
Publication No. 5227-0915
September 2015

Eaton's Crouse-Hinds business
1201 Wolf Street
Syracuse, NY 13208
Crouse-Hinds.com
(866) 764-5454
crouse.customerctr@cooperindustries.com

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Extra duty
while-in-use covers
for outdoor environments

Extra Duty While-in-Use Covers



TP7488XD



TP7488XDW



TP7487XD



TP7489XD



Applications:

- Commercial and residential landscape lighting, vending machines, etc.
- Seals out moisture and sheds water, ice and snow
- Meets or exceeds outdoor low voltage requirements

Description:

- 1-gang easy-to-close cover for horizontal applications
- 1-gang easy-to-close cover for vertical applications
- 2-gang easy-to-close cover for either horizontal or vertical applications

Features:

- Meets NEC® and CEC® extra duty requirements for any application
- Rugged UV-resistant polycarbonate cover and back protects devices without cracking or breaking and is non-corrosive
- Robust design with stainless steel reinforced hinge
- Easy-to-close padlockable cover
- Box inserts accommodate decorator and GFCI devices, duplex receptacles, and a variety of single receptacle sizes and toggle switches
 - 1-gang box includes 3 inserts for 8 different configurations
 - 2-gang box includes 4 inserts for over 60 different configuration
- Cover cord opening fits #12 AWG or small gauge
- Cover depth is 3-1/4"
- Box cover includes pre-mounted gasket
- Listed for use in wet locations



Certification and Compliances:

- cULus Listed to UL514D
- UL File # E-102328
- Meets 2014 NEC® 406.9 and CEC® Rule 26-702
- NEMA 3R

Standard Materials & Finishes:

- Clear cover, body and cover plates – polycarbonate
- Gasket – ethylene vinyl acetate (EVA)
- Hinge pin – stainless steel

Extra Duty While-in-Use Weather Protective Covers

Cat. #	Gang	Mounting Description	Material	Color	Depth
TP7488XD	1	Horizontal	Polycarbonate	Gray	3-1/4"
TP7488XDW	1	Horizontal	Polycarbonate	White	3-1/4"
TP7487XD	1	Vertical	Polycarbonate	Gray	3-1/4"
TP7487XDW	1	Vertical	Polycarbonate	White	3-1/4"
TP7489XD	2	Horizontal/Vertical	Polycarbonate	Gray	3-1/4"
TP7489XDW	2	Horizontal/Vertical	Polycarbonate	White	3-1/4"

Color Information



Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2015 Eaton
All Rights Reserved
Printed in USA
Publication No. 5227-0915
September 2015

Eaton's Crouse-Hinds business

1201 Wolf Street
Syracuse, NY 13208
Crouse-Hinds.com
(866) 764-5454
crouse.customerctr@cooperindustries.com

Eaton is a registered trademark.

All other trademarks are property of their respective owners.