## Specifications



Photo is representative

## Eaton UAT2R2332UFLCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #6-350 kcmil, 4-jaw, 1phase, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

| General specifications  |   |
|-------------------------|---|
| PRODUCT NAME            | Eaton meter socket  |
| CATALOG NUMBER          | UAT2R2332UFLCH  |
| UPC                     | 782116997817  |
| PRODUCT<br>LENGTH/DEPTH | 5.38 in   |
| PRODUCT HEIGHT          | 14.13 in  |
| PRODUCT WIDTH           | 24.31 in  |
| PRODUCT WEIGHT          | 29 lb   |
| WARRANTY                | Eaton Selling Policy 25-<br>000, one (1) year from the<br>date of installation of the<br>Product or eighteen (18)<br>months from the date of<br>shipment of the Product,<br>whichever occurs first. |
| CERTIFICATIONS          | UL Listed   |



| Product specifications |  |
|------------------------|--|
| ТҮРЕ                   | Multiple position residential service  |
| AMPERAGE RATING        | 200A   |
| FEED TYPE              | Top/bottom   |
| NUMBER OF JAWS         | Four-jaw   |
| PHASE                  | Single-phase   |
| ENCLOSURE              | 063 aluminum   |
| UTILITY APPROVALS      | FL: MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN: MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY: MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric, Gulf Power, Oklahoma Gas and Electric) NC: MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH: MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC: MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC: MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) TL: Tallahassee City Electric |
| LINE                   | #6-350 kcmil   |
| LOAD                   | #8-250 kcmil   |
| NUMBER OF WIRES        | Three-wire   |
| НИВ ТҮРЕ               | Hub cover plate  |
| CONNECTION             | Ground connection  |
| SECURITY               | Ringless   |
| VOLTAGE RATING         | 600 V  |
| NUMBER OF SOCKETS      | 2  |

| Resources                     |   |
|-------------------------------|---|
| CATALOGS                      | Residential and Light<br>Commercial, Metering<br>Products, Volume 1 Tab 4 |
| SPECIFICATIONS AND DATASHEETS | <u>Eaton Specification Sheet -</u><br><u>UAT2R2332UFLCH</u>               |

| PROJECT NAME:   |  |
|-----------------|--|
| PROJECT NUMBER: |  |
| PREPARED BY:    |  |
| DATE:           |  |



**Eaton Corporation plc** Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.









