

# Eaton UAT4R2352UFLCH

Catalog Number: UAT4R2352UFLCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #1/0-500 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

## General specifications



Photo is representative

**Product Name**

Eaton meter socket

**UPC**

782116997831

**Product Height**

14.125 in

**Product Weight**

49 lb

**Certifications**

UL Listed

**Catalog Number**

UAT4R2352UFLCH

**Product Length/Depth**

5.375 in

**Product Width**

40.625 in

**Warranty**

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Catalog Notes**

FMG approved

## defaultTaxonomyAttributeLabel

### Type

Multiple position residential service

### Amperage Rating

200A

### Feed type

Top/bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

### Line

#1/0-500 kcmil

### Load

#8-250 kcmil

### Enclosure material

Aluminum

### Number of wires

Three-wire

### Connection

Ground connection

### Security

Ringless

### Voltage rating

600 V

## Resources

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Drawings

[Dimensional Drawing - SKT/4 GANG 200A 1P HCP](#)

### Specifications and datasheets

[Eaton Specification Sheet - UAT4R2352UFLCH](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton UAT4R2352UFLCH

Catalog Number: UAT4R2352UFLCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #1/0-500 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

## General specifications



Photo is representative

**Product Name**

Eaton meter socket

**UPC**

782116997831

**Product Height**

14.125 in

**Product Weight**

49 lb

**Certifications**

UL Listed

**Catalog Number**

UAT4R2352UFLCH

**Product Length/Depth**

5.375 in

**Product Width**

40.625 in

**Warranty**

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Catalog Notes**

FMG approved

## defaultTaxonomyAttributeLabel

### Type

Multiple position residential service

### Amperage Rating

200A

### Feed type

Top/bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

### Line

#1/0-500 kcmil

### Load

#8-250 kcmil

### Enclosure material

Aluminum

### Number of wires

Three-wire

### Connection

Ground connection

### Security

Ringless

### Voltage rating

600 V

## Resources

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - SKT/4 GANG 200A 1P HCP

### Specifications and datasheets

Eaton Specification Sheet - UAT4R2352UFLCH

### Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)