



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WGRB Wingtwistgrounding Connector, WGR Green, 250/Carton *Ideal*

Catalog Number	WGRB
Manufacturer	Ideal
Description	Buchanan, Wire Connector, Wingtwist, Conductor Range: 14 - 10 Awg, 2/14 Awg Min, 5/12 Awg Max, Number Of Conductors: 2 to 5, Material: Flame-Retardant Polypropelene, Color: Green, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WGR
Weight per unit	1.9 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant Polypropelene
Number of Conductors	2 to 5
Voltage Rating	600

Material, Color, and Finish

Color	Green
-------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	WINGTWISTGROUNDING CONNECTOR,WGR GREEN,250/CARTON
extra long description	IDEAL WGR-B WGR GREEN GROUND CAP 25
Features	With a full line for virtually every wire size and combination, the WingTwist Wire Connector offers a great combination of performance and value.The contoured wing design of the WingTwist provides maximum torque for a variety of electrical applications while the copolymer shell and live-action spring expand for smooth, progressive tightening providing dependable connections.With a tough, flame-retardant shell that withstands environmental extremes, and a long, deep skirt to provide maximum dielectric prote
Long Description	Buchanan, Wire Connector, WingTwist, Conductor Range: 14 - 10 AWG, 2/14 AWG Min, 5/12 AWG Max, Number Of Conductors: 2 to 5, Material: Flame-retardant Polypropelene, Color: Green, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WGR
Product Type	WGR Green Ground Cap 250 Box
Special Features	1,000V Maximum In Fixtures And Signs;Contoured Wing Design Provides Maximum Torque;Deep Skirt Protects Against Flash-Over;Expanding, Square-Wire Spring Creates Secure Connections;Features: Five Color-Coded Models Cover Common Construction Wire Ranges And Combinations, Including Grounding;Model Number: WGR

Manufacturer Information

Brand	Buchanan
GTIN	00781789470078
Manufacturers Part Number	WGR-B
sub brand	WingTwist
UPC	781789470078

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	--

Availability

minimum qty	250
-------------	-----

Packaging

Carton	250
Weight Per each	1.85



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	For Grounding And Bonding Applications
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 467 Listed, RoHS