


ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

700 Industry Way Suite 10 75078-0000, TX Prosper Phone: 469-899-3981 Fax: 469-899-3982





WW722YL 3/4"X60' Ylw SLCT Vny Tape Nsi Industries

Catalog Number	WW722YL
Manufacturer	Nsi Industries
Description	Warriorwrap WW-722-YI Yellow Vinyl Professional Electrical Tape Is Strong Enough For Demanding Environments and Highly Resistant to Abrasion and Corrosion. This Tape Is 7MIL Thick, 60FT Long and Has A Max Temperature Rating Of 176 Degrees. The Strong Adhesion Helps Stick to Uneven Surfaces and Keeps The Backing In Place. Top Breaking Strength and Elasticity Make Warriorwrap An Excellent Choice For Splicing, Insulating or Marking Wires.
Weight per unit	0.1900 (lbs/each)
Product Category	Markers & Marking Tapes
Features	
adhesion strength	22
Material	Vinyl
maximum voltage	600
Temperature Range	20° - 176°
Tensile Strength	17
Warranty	1 YEAR
Material, Color, and Finish Backing Material	Plasticized Polyvinyl Chloride (PVC)
Color	Yellow
Dimensions and Weight	40
Length	60
Size	Thickness - 7mil - Length-60' - Width 3/4"
Thickness	.007
Width	.75



Uses, Certifications, and Standards Application

standard

ELLIOTT ELECTRIC SUPPLY 700 Industry Way Suite 10 75078-0000, TX Prosper Phone: 469-899-3981 Fax: 469-899-3982

Descriptions	
Descriptions	3/4"X60' YLW SLCT VNY TAPE
Description extra long description	NSI WW-722-YL Vyl Elec Tape Select
Features	Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge.For insulating, splicing or marking cables and wires on the jobsite, choose WarriorWrap, available in 12 colors and 3 grades of quality. That quality starts with strong adhesion to stick to uneven surfaces. But that's not allâ€″it also features the best breaking strength around and unmatched elasticity to hold tight in residential or commercial en
Long Description	WarriorWrap WW-722-YL Yellow Vinyl Professional Electrical Tape is strong enough for demanding environments and highly resistant to abrasion and corrosion. This tape is 7mil thick, 60ft long and has a max temperature rating of 176 degrees. The strong adhesion helps stick to uneven surfaces and keeps the backing in place. Top breaking strength and elasticity make WarriorWrap an excellent choice for splicing, insulating or marking wires.
Product Type	Vyl Elec Tape Select 7MIL .75" 60FT YI
Special Features	Excellent Adhesion and Elasticity, All Weather Performance, High Tensile Strength, Resistant to UV, Abrasion and Corrosion, Flae-Retardant.
Manufacturer Information	
Brand	NSi
GTIN	00662381367303
Manufacturers Part Number	WW-722-YL
UPC	662381367303
Taxonomies, Classifications, and Cate	gories
Category Description	TAPE
Type	Select Purpose
Packaging	•
Carton	1
Weight Per each	0.19
•	

NSI

UL 510