



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EW120BC 7-Day M-Purp CNTRL *Nsi Industries*

Catalog Number	EW120BC
Manufacturer	Nsi Industries
Description	Tork 7 Day 1 Channel SPDT Digital Time Switch Applications: Outdoor Signs Heating and Air Conditioning Lighting Security Features: Input Supply: 120-277 Vac 50/60HZ Input Voltage: 120-277 Vac 50/60HZ Output Dry Contacts: SPDT Power Consumption: 6VA Max. Timing Accuracy: Line Frequency Scheduling: 20 On/Off Set Points Repeat Each Day. Minimum Setting 1 Minute. No. Of Channels: 1 Channel Daylight Savings: Automatic Adjustment (Can Be Omitted) Leap Year: Automatic Compensation Manual Override: Until The Next
Weight per unit	1.5 (lbs/each)
Product Category	Controls

Features

action	SPDT
Base	Screw
Contact Rating	120-277 VAC
Phase	Single Phase
Poles	1
Timing Range	7 DAY

Dimensions and Weight

Size	L=5.062 - H=8.312 - W=3.062
------	-----------------------------

Descriptions

Description	7-DAY M-PURP CNTRL
extra long description	TORK EW120B-C Digital Timer SPDT CI
Long Description	Tork 7 Day 1 Channel SPDT Digital Time Switch APPLICATIONS: Outdoor Signs Heating and Air Conditioning Lighting Security FEATURES: INPUT SUPPLY: 120-277 VAC 50/60Hz INPUT VOLTAGE: 120-277 VAC 50/60Hz OUTPUT DRY CONTACTS: SPDT POWER CONSUMPTION: 6VA Max. TIMING ACCURACY: Line Frequency SCHEDULING: 20 ON/OFF set points repeat each day. Minimum Setting 1 minute. NO. OF CHANNELS: 1 Channel DAYLIGHT SAVINGS: Automatic adjustment (can be omitted) LEAP YEAR: Automatic Compensation MANUAL OVERRIDE: Until the next
Product Type	Digital Timer SPDT Clear
Special Features	20 On-Off Set Points - Daylight Savings Auto - Leap Year Automatic Compensation



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	NSi
GTIN	00786261824370
Manufacturers Part Number	EW120B-C
UPC	786261824370

Taxonomies, Classifications, and Categories

Category Description	TIMERS
Type	7 Day Time Switch - 1 Or 2 Channel

Packaging

Carton	1
Weight Per each	1.5

Uses, Certifications, and Standards

Application	NSI
Enclosure	NEMA 3R Plastic Indoor-Outdoor With Clear Cover
environmental conditions	-40 to + 149 F
Frequency Rating	50-60 Hz
Mounting	Screw Mount
Operating Temperature	-40 to + 149 F
standard	cULus