


NEMA Flanged Panels Accessories

NEMA Flanged Panel Catalog Number				A		B		Gauge	Fits Enclosure Height x Width	
Painted Steel	Galvanized Steel	Stainless	Aluminum	in.	mm	in.	mm		in.	mm
AW2420P	AW2420GP	AW2420SP	AW2420AP	20.87	530	16.87	428	12	24.00"x20.00"	610x508
AW2424P	AW2424GP	AW2424SP	AW2424AP	20.87	530	20.87	530	12	24.00"x24.00"	610x610
AW3016P	AW3016GP	AW3016SP	AW3016AP	26.87	682	12.87	327	12	30.00"x16.00"	762x406
AW3020P	AW3020GP	AW3020SP	AW3020AP	26.87	682	16.87	428	12	30.00"x20.00"	762x508
AW3024P	AW3024GP	AW3024SP	AW3024AP	26.87	682	20.87	530	12	30.00"x24.00"	762x610
AW3030P	AW3030GP	AW3030SP	AW3030AP	26.87	682	26.87	682	12	30.00"x30.00"	762x762
AW3624P	AW3624GP	AW3624SP	AW3624AP	32.87	835	20.87	530	12	36.00"x24.00"	914x610
AW3630P	AW3630GP	AW3630SP	AW3630AP	32.87	835	26.97	685	12	36.00"x30.00"	914x762
AW3636P	-	AW3636SP	-	32.87	835	32.87	835	12	36.00"x36.00"	914x914
AW4224P	-	-	-	38.87	987	20.87	530	12	42.00"x24.00"	1067x610
AW4230P	AW4230GP	AW4230SP	AW4230AP	38.87	987	26.87	682	12	42.00"x30.00"	1067x762
AW4236P	AW4236GP	AW4236SP	AW4236AP	38.87	987	32.87	835	12	42.00"x36.00"	1067x914
AW4242P	-	-	-	38.87	987	38.87	987	12	42.00"x42.00"	1067x1067
AW4824P	-	-	-	44.87	1140	20.87	530	12	48.00"x24.00"	1219x610
AW4830P	AW4830GP	AW4830SP	-	44.47	1130	26.87	682	12	48.00"x30.00"	1219x762
AW4836P	AW4836GP	AW4836SP	AW4836AP	44.87	1140	32.87	835	12	48.00"x36.00"	1219x914
AW4842P	AW4842GP	AW4842SP	AW4842AP	44.87	1140	38.87	987	12	48.00"x42.00"	1219x1067
AW4848P	-	-	-	44.87	1140	44.87	1140	12	48.00"x48.00"	1219x1219
AW6030P	-	-	-	56.87	1444	26.87	682	12	60.00"x30.00"	1524x762
AW6036P	AW6036GP	AW6036SP	AW6036AP	56.87	1444	32.87	835	12	60.00"x36.00"	1524x914
AW6042P	-	-	-	56.87	1444	38.87	987	12	60.00"x42.00"	1524x1067
AW7230P	-	-	-	68.87	1749	26.87	682	12	72.00"x30.00"	1829x762
AW7236P	-	-	-	68.87	1749	32.87	835	12	72.00"x36.00"	1829x914

* Panel also fits these enclosures when height and width dimensions are reversed.



NEMA Flanged Panels can be installed in consoles, Type 4X, Type 4, and Type 12 NEMA Enclosures. Panels are available in steel, galvanized steel, stainless steel and aluminum. Painted steel panels have a white powder paint finish. Stainless steel and aluminum panels have a smooth brushed finish on one side and protected with PVC film.

Notes: Dimensions are in inches. Millimeters shown are for reference only. Data subject to change without notice.