



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



XTOR8B 81W Led Wallpack 50K 8502LM

Cooper Lighting Solutions

Catalog Number	XTOR8B
Manufacturer	Cooper Lighting Solutions
Description	Crosstour Maxx, Led 81W, Wall Mount, Full Cutoff Door, 5000K, 120-277V, Carbon Bronze
Weight per unit	12.3 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.71 (at 120V)/0.31 (at 277V)
Ballast Type	N/A
Lamp Included	Yes
Lamp Type	LED
Material	Die-Cast Aluminum
Number of Lamps	1
Socket Type	N/A
Voltage Rating	120-277V
Wattage	81 W

Material, Color, and Finish

Finish	Carbon Bronze
Style	(blank)

Descriptions

Description	81W LED WALLPACK 50K 8502LM
extra long description	CLS XTOR8B CBN BZ,80W,5000K,120-277
Long Description	Crosstour MAXX, LED 81W, Wall Mount, Full Cutoff Door, 5000K, 120-277V, Carbon Bronze
Product Type	CBN BZ, 80W, 5000K, 120-277V
Special Features	Wall, inverted or pole mount. Energy saving replacement up to 400W HID

Manufacturer Information

Brand	LUMARK
GTIN	00080083774814
Manufacturers Part Number	XTOR8B
UPC	080083774814

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	WALL MOUNT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	2
Weight Per each	12.3

Uses, Certifications, and Standards

Application	lighting
Mounting	Wall/Surface Mount
standard	UL/cUL Listed - Wet Location;3G Vibration Tested;IP66 Rated;NOM Compliant;DLC Qualified;LM79/LM80 Compliant;DLC Premium;40 Degree C Ambient Temperature Rating;Dark Sky Compliant;RoHS Compliant