



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA1CL2 1AWG Cop Lug *Burndy LLC*

Catalog Number	YA1CL2
Manufacturer	Burndy LLC
Description	1 Awg Cu, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Green Color Code, 11 or 375 Die Index.
Weight per unit	0.0400 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	11
Material	Copper
pallet quantity	46400
Voltage Rating	35

### Material, Color, and Finish

Color Code	GREEN
------------	-------

### Descriptions

Description	1AWG COP LUG
extra long description	BUR YA1CL2 1STR CU 1-HOLE SHORT 1/4
Long Description	1 AWG CU, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, GREEN Color Code, 11 or 375 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Die Index: 11, Wire Strip Length: 15/16 IN, Tongue Angle: Straight, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W1CVT, W1CRT-1, X1CRT-1 Die, (1), Hydraulic: BCT500HS, Y500CTHS Tool, W1CVT, W1CRT-1, X1CRT-1 Die, (1), Y35, Y39, Y750, PAT750 Tool, U1CRT-1, U4CABT Die, (1), Y46 Tool, U1CRT-1, U4CABT Die With PUADP-1 Adap

### Manufacturer Information

Brand	BURNDY
GTIN	00781810551264
Manufacturers Part Number	YA1CL2
UPC	781810551264

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.04

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B