



X-Treme Box™



01950



01960



01962

The X-Treme Box™ is a portable, flexible, rugged and reliable power distribution center for all jobsite conditions. It is an economical solution for electrical hook up on any worksite. For expandability, run up to four boxes at 400ft. in series before significant voltage drop occurs. A heavy-gauge carbon-steel case with corrosion resistant finish and a steel-reinforced sled base offer excellent durability. The X-Treme Box™ offers the most advanced GFCI technology to virtually eliminate the possibility of electrical shock. All boxes feature seven overload protected outlets, with GFCI, open neutral and over-voltage protection on all 20A outlets. Model 1950 is used where water is not likely to enter the enclosure. Models 1960 and 1970 are Rainproof NEMA 3R enclosures. New roll cage versions allow for easy stackability.

Applications: Commercial – for Indoor/outdoor construction residential, renovation and demolition. Entertainment – for stage, concerts, broadcasting and cinema. Institution – for sports, special events and convention centers.

Compliance: ETL Listed US and Canada.

CAT NO	PORTABLE POWER DISTRIBUTION CENTER	50A POWER INLET	50A POWER OUTLETS	30A POWER OUTLET	20A POWER OUTLETS	OVERLOAD, OVER-VOLTAGE & OPEN-NEUTRAL PROTECTION	MASTER PACK	MASTER WT	MASTER PACK CUBE
01950	NEMA Type 1	125/250v Twist-To-Lock	125/250v Twist-To-Lock	250v L6-30R Twist-To-Lock w/Cover	(6) 20A 125v L5-20R Twist-To-Locks w/Cover	50A-None 30A Circuit Breaker Protected 20A GFCI & Circuit Breaker Protected	1	34	2.54
01960	Rainproof NEMA 3R	125/250v Twist-To-Lock w/Cover	125/250v Twist-To-Lock w/Cover	250v L6-30R Twist-To-Lock w/Cover	(6) 20A 125v L5-20R Twist-To-Locks w/Cover	50A-None 30 A Circuit Breaker Protected 20A GFCI & Circuit Breaker Protected	1	34	2.54
01962	Roll Cage Model (Electrical specs are identical to part no. 01960)								
01970	Rainproof NEMA 3R	125/250v Twist-To-Lock w/Cover	125/250v Twist-To-Lock w/Cover	250v L6-30R Twist-To-Lock w/Cover	(6) 20A 125v 5-20R Straight Blades w/Cover	50A - None 30A Circuit Breaker Protected 20A GFCI & Circuit Breaker Protected	1	34	2.54
01972	Roll Cage Model (Electrical specs are identical to part no. 01970)								

Power Distribution Extension Cords



Rugged temporary power cords are designed for use with the X-Treme Box™ to handle 50A 3-Pole/4-Wire 125/250v AC.



01938

CAT NO	50A 6/3 & 8/1 125/250V CORD SETS	MASTER PACK	MASTER WT	MASTER PACK CUBE
01918	50ft SEOW w Marinco Ends	1	27	.75
01919	100ft SEOW w Marinco Ends	1	54	1.3
01938	50ft SEOW w Hubbell Ends	1	27	.75
01939	100ft SEOW w Hubbell Ends	1	54	1.3

Replacement Ends/Adapters

Replacement ends are constructed with impact and chemical resistant nylon and designed to keep out moisture and dust.



05958

05959



05974

05975

CAT NO	50A 3-POLE/4-WIRE 125/250V PLUGS/CONNECTORS/ADAPTERS	MASTER PACK	MASTER WT	MASTER PACK CUBE
05974*	50A Marinco Male Plug	4	2	.26
05975*	50A Marinco Female Connector	4	2	.26
05958*	50A Hubbell Male Plug	4	2	.26
05959*	50A Hubbell Female Connector	4	2	.26
01920	6/4 SEOW 50A "Y" Adapter	1	4	2.25

* UL and CSA Listed