

**Open Switches**  
**T&B Catalog Number:**

OT25FT3  
80432541546  
Active

**UPC Number:****Status:****Description:**

3 pole, 25 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

**Features**

Quick make, quick brake mechanism  
Extremely compact size  
Finger-proof construction with no hazardous exposed parts

**Application**

Industrial control panel disconnects  
For use in motor controller and motor overload protection applications  
Can be used as an OSHA lockout/tagout disconnect

**General**

Style	Door Mounted
Number of Poles	3
Series	Non-fusible

**Approvals**

UL Class	UL 508
----------	--------

**Dimension Information**

H x W x D (inches)	2.13 x 1.69 x 2.64
--------------------	--------------------

**Specifications**

Rated Current (Amps)	25
Rated Voltage AC	600

**Packaging**

T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	0.23 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)

**Open Switches**  
**T&B Catalog Number:**OT25FT3  
80432541546  
Active**UPC Number:****Status:****Description:**

3 pole, 25 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

**Features**

Quick make, quick brake mechanism
Extremely compact size
Finger-proof construction with no hazardous exposed parts

**Application**

Industrial control panel disconnects
For use in motor controller and motor overload protection applications
Can be used as an OSHA lockout/tagout disconnect

**General**

Style	Door Mounted
Number of Poles	3
Series	Non-fusible

**Approvals**

UL Class	UL 508
----------	--------

**Dimension Information**

H x W x D (inches)	2.13 x 1.69 x 2.64
--------------------	--------------------

**Specifications**

Rated Current (Amps)	25
Rated Voltage AC	600

**Packaging**

T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	0.23 lbs. Each

**For further technical assistance, please contact us...**Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.comT&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com