

Eaton MB816B200BTS

Catalog Number: MB816B200BTS

Eaton resi meter breaker, feed through lugs, All-in-ones, 200 A, C, Aluminum, NEMA 3R, Bottom and top, #6-350 kcm10 kAIC, #6-350 kcmCSR2200, Surface mounting, 16, Four-jaw, 1, 8, Single-phase, Ringless, Used with BR breakers, 120/240 Vac

General specifications

Product Name	Catalog Number
Eaton residential meter breaker	MB816B200BTS
UPC	Product Length/Depth
782114858615	5.38 in
Product Height	Product Width
32.38 in	14.44 in
Product Weight	Warranty
40.62 lb	10 year
Certifications	
UL Listed	



Product specifications

Interrupt rating

10 kAIC

Utility approvals

ME : Central Maine Power

NC : Dominion

VA : Dominion

MO : Empire District Electric

OK : Empire District Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

MD : First Energy (Potomac Edison)

VA : First Energy (Potomac Edison)

WV : First Energy (Mon Power)

NJ : First Energy (Jersey Central Power and Light)

OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company)

PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power)

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NY : Rochester Gas & Electric (RG&E)

AL : Alabama Power

Phase

Single-phase

Ground

#6-350 kcmil

Bus material

Aluminum

Number of jaws

Four-jaw

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER BREAKER EAST COAST STYLE

Specifications and datasheets

Eaton Specification Sheet - MB816B200BTS

Technical Data Residential Meter Breakers: Type CH and BR Residential

Main circuit breaker

CSR2200

Enclosure

NEMA 3R

Type

All-in-ones

Feed type

Top/bottom

Number of sockets

1

Voltage rating

120/240 V

Number of circuits

16

Box size

C



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)