









Folding Utility Knives

CAT NO.	UPC NO.	DESCRIPTION	FEATURES & BENEFITS	QTY.
0652-22	00041	Folding Utility Knife 	<ul style="list-style-type: none"> High finish stainless steel handle with molded features for added comfort in rugged environments Quick-change locking blade holder and lock-back feature for added safety and convenience Belt clip adds convenience Includes 10 extra blades Uses standard utility blades 	1
0652-23	00043	Folding Utility Knife, Heavy-Duty 	<ul style="list-style-type: none"> Heavy-Duty aluminum housing with built-in blade storage for added convenience Larger handle shape improves ergonomics Thumb pad allows safe position to apply extra cutting force comfortably Quick-change locking blade holder and lock-back feature for added safety and convenience Includes storage pouch and 5 extra blades Uses standard utility blades 	1

Greenlee Knives by Old Timer®

CAT NO.	UPC NO.	DESCRIPTION	SPECIFICATIONS	FEATURES & BENEFITS	QTY.
0652-24	00057	Drop Point Pocket Knife, Wood 	Blade: 440C Stainless Steel Blade Length: 2.25" (57 mm) Blade Safety: Lock-back Handle Size: 3.50" (89 mm) Handle Material: Desert Ironwood with stainless bolsters and belt clip	<ul style="list-style-type: none"> Stainless steel blade for extra durability and corrosion resistance Premium finish Desert Ironwood handle contoured for comfortable hand fit Belt clip for added convenience Lock-back for increased safety 	1
0652-25	00058	Titanium-Coated Drop Point Pocket Knife, Aluminum 	Blade: Titanium coated 440C Stainless Steel <ul style="list-style-type: none"> 40% serrated Blade Safety: Lock-back Handle Size: 3.50" (89 mm) Handle Material: Anodized aluminum with reversible belt clip and lanyard hole	<ul style="list-style-type: none"> Titanium coated stainless steel blade for premium durability and corrosion resistance 40% serrated edge for tough cutting jobs Aircraft-grade aluminum handle to endure extra rough handling Ambidextrous thumb-stud and reversible belt clip for added convenience Lock-back for increased safety 	1
0652-26	00059	Coping Blade 	Blade: 440C Stainless Steel Blade Length: 2.25" (57 mm) Blade Safety: Lock-back Handle Size: 3.25" (82 mm) Handle Material: Rosewood with stainless bolsters and swivel ring	<ul style="list-style-type: none"> Stainless steel blade for extra durability and corrosion resistance Premium finish rosewood handle Lock-back for increased safety Swivel ring for attachment option 	1
0652-27	00060	Hawkbill Pocket Knife, Molded Handle 	Blade: 440C Stainless Steel Blade Length: 2.63" (67 mm) Blade Safety: Lock-back Handle Size: 4.00" (101 mm) Handle Material: Hi-impact plastic/rubber with lanyard hole	<ul style="list-style-type: none"> Stainless steel blade for extra durability and corrosion resistance Dual-material molded handle contoured for sure and comfortable fit Belt clip for added convenience Lock-back for increased safety 	1
0652-28	00061	Hawkbill Pocket Knife, Wood Handle 	Blade: 440C Stainless Steel Blade Length: 2.63" (67 mm) Blade Safety: Lock-back Handle Size: 4.00" (101 mm) Handle Material: Rosewood with swivel ring	<ul style="list-style-type: none"> Stainless steel blade for extra durability and corrosion resistance Premium finish rosewood handle contoured for comfortable hand fit Belt clip for added convenience Lock-back for increased safety 	1
0652-29	00062	Hawkbill Fixed Blade w/Sheath 	Blade: 440C Stainless Steel Blade Length: 3.00" (76 mm) <ul style="list-style-type: none"> Fixed Handle Size: 7.80" (198 mm) Handle Material: Full-length solid tang with Rosewood facing, stainless bolster and lanyard hole Sheath: Reinforced nylon with belt loop	<ul style="list-style-type: none"> Stainless steel blade for extra durability and corrosion resistance Fixed blade with solid tang runs full length of handle to provide the highest strength and reliable handling Premium finish rosewood handle contoured for comfortable hand fit Nylon sheath with belt loop for convenient accessibility 	1

DISTRIBUTOR INFORMATION:

Schrade® and Old Timer® are registered trademarks of Taylor Brands, LLC.

GREENLEE®
A Textron Company

www.greenlee.com • MA-5660 08/11
4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070
©2011 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA
Greenlee Textron Inc. is a subsidiary of Textron Inc.

USA

Tel: 800.435.0786
Fax: 800.451.2632

CANADA

Tel: 866.384.8813
Fax: 800.524.2653

INTERNATIONAL

Tel: +1.815.397.7070
Fax: +1.815.397.9247

