



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

317 S Mercedes Ave
85122-0000, AZ Casa Grande
Phone: 520-677-1167
Fax: 000-000-0000



OTM6 250V 6A 1 1/2X13/32 Mid Fuse

Mersen Fuses

Catalog Number	OTM6
Manufacturer	Mersen Fuses
Description	Fuse Otm - Midget - Fast-Acting 250VAC 6A Ferrule Amp-Trap®
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Features

AC Voltage Rating	250
amperage rating	6
class	Midget
connection	Ferrule
Fuse Class	Midget
interrupt rating	10
Voltage Rating	250

Material, Color, and Finish

Body Material	Paper
---------------	-------

Dimensions and Weight

Size	1.5 x 0.41
------	------------

Descriptions

Description	250V 6A 1 1/2X13/32 MID FUSE
extra long description	Mersen OTM6 Fuse OTM - Midget - Fas
Features	One-Time OTM midget fuses provide low-cost protection for 250VAC general purpose lighting, heating, control circuits, etc. where time-delay is not required. (Not for Branch Circuit Protection).
Long Description	Fuse OTM - Midget - Fast-Acting 250VAC 6A Ferrule Amp-Trap®
Product Type	Sicherungseinsatz Otm – Miniatur – Flink 250VAC 6A Kapselsic
Short Description	250V 6A 1 1/2x13/32 MID FUSE
Special Features	Low cost and fully rated for economy without compromise Can be used with UltraSafe™ fuse holders 1 1/2" x 13/32" (10 mm x 38 mm) dimensions

Manufacturer Information

Brand	Mersen
GTIN	00782001705060
Manufacturers Part Number	OTM6
UPC	782001705060



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

317 S Mercedes Ave
85122-0000, AZ Casa Grande
Phone: 520-677-1167
Fax: 000-000-0000

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	Midget Fuses

Packaging

Carton	1
Package	10
Weight Per each	0.01

Uses, Certifications, and Standards

Application	Supplemental protection of circuits up to 250VAC and 10kA
Mounting standard	Clip UL Listed to standard 248-14, File E33925 CSA Certified to Standard C22.2 No. 248.14